

**UNIVERSAL STRIP SOLAR****Article No.:** 21920120Stripping tool; Conductor cross-section 1.5mm<sup>2</sup> - 6mm<sup>2</sup>;**Details****Notes**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Trade product, not a LAPP product.

**Remarks**

Trade product, not a LAPP product.

---

 Technical Data

**General information**

Product type	Stripping tool
Scope of delivery	including knife
Delivery Unit	1
suitable for	Solar cables

**Electrical parameters**
**Product design**

Total length	7.638 in
For cross-section (min.)	1.5 mm <sup>2</sup>
For cross-section (max.)	6 mm <sup>2</sup>
Surface protection	Chrome-plated
Colour description	orange
For insulation material	Polyolefin

**Product features**
**Certifications and standards**

CE marking	No
VDE certified	No
TÜV certified	No

**UNIVERSAL STRIP stripping tool**

Article No.	Name	For cross-section (min.)	For cross-section (max.)	For insulation material	Product type
21920004	UNIVERSAL STRIP BLADE PTFE 2.5-10	2.5 mm <sup>2</sup>	10 mm <sup>2</sup>	Polytetrafluoroethylene	Knife
21920005	UNIVERSAL STRIP W.OUT STRIPPING BLADE				Stripping tool
21920006	UNIVERSAL STRIP BLADE PTFE 0.03-2.08	0.03 mm <sup>2</sup>	2.08 mm <sup>2</sup>	Polytetrafluoroethylene	Knife
21920009	UNIVERSAL STRIP BLADE PVC 0.14-6	0.14 mm <sup>2</sup>	6 mm <sup>2</sup>	Polyvinylchloride	Knife
21920120	UNIVERSAL STRIP SOLAR	1.5 mm <sup>2</sup>	6 mm <sup>2</sup>	Polyolefin	Stripping tool
21920122	UNIVERSAL STRIP BLADE SOLAR 1.5-6	1.5 mm <sup>2</sup>	6 mm <sup>2</sup>	Polyolefin	Knife
21920140	UNIVERSAL STRIP ASI			Thermoplastic elastomers,Polyvinylchloride	Stripping tool

V1.1