

UNIVERSAL STRIP ASI**Article No.:** 21920140

Stripping tool;

**Details****Notes**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Trade product, not a LAPP product.

Remarks

Trade product, not a LAPP product.

Technical Data

General information

Product type	Stripping tool
Delivery Unit	1
suitable for	AS-Interface

Electrical parameters

Product design

Total length	7.638 in
Surface protection	Chrome-plated
Colour description	orange
For insulation material	Thermoplastic elastomers Polyvinylchloride

Product features

Certifications and standards

CE marking	No
VDE certified	No
TÜV certified	No

UNIVERSAL STRIP stripping tool

Article No.	Name	For cross-section (min.)	For cross-section (max.)	For insulation material	Product type
21920004	UNIVERSAL STRIP BLADE PTFE 2.5-10	2.5 mm ²	10 mm ²	Polytetrafluoroethylene	Knife
21920005	UNIVERSAL STRIP W.OUT STRIPPING BLADE				Stripping tool
21920006	UNIVERSAL STRIP BLADE PTFE 0.03-2.08	0.03 mm ²	2.08 mm ²	Polytetrafluoroethylene	Knife
21920009	UNIVERSAL STRIP BLADE PVC 0.14-6	0.14 mm ²	6 mm ²	Polyvinylchloride	Knife
21920120	UNIVERSAL STRIP SOLAR	1.5 mm ²	6 mm ²	Polyolefin	Stripping tool
21920122	UNIVERSAL STRIP BLADE SOLAR 1.5-6	1.5 mm ²	6 mm ²	Polyolefin	Knife
21920140	UNIVERSAL STRIP ASI			Thermoplastic elastomers,Polyvinylchloride	Stripping tool

V1.1