

AB-C4-M8MS-1,0PUR-M8FS
Article No.: 22260315

Pre-assembled sensor/actuator cable; Cable chain, Flexible; Polyurethane; 1x4; M 8 (A-coded), Plug, Straight (180 °); M 8 (A-coded), Socket, Straight (180 °); 1 m



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	UNITRONIC®
Product type	Pre-assembled sensor/actuator cable
Length	1 m
Delivery Unit	1

Connector 1	M 8; Plug; Straight; A-coded; Number of contacts: 4
Connector 2	M 8; Socket; Straight; A-coded; Number of contacts: 4
valid Fieldbus or Ethernet System	Sensor/Actuator

Electrical parameters

Product design

Cable dimension	4X
Including protective ground	No
Number of cores	4
Shielded	No
Coded	Yes
Base material of outer sheath, shortname	PUR

Product features

Application area	Cable chain
Min. number of insertion cycles	100
IP protection rating	IP 65 IP 67 IP 68
Suitable for EX-applications	No

Certifications and standards

CE marking	Yes
EAC certified	Not required
EAC certification number	Отказное письмо № 40
UL recognized	No
UL listed	Yes
UL certification	according to UL 2238 (e-file number: E249137)
cUR recognized	No

cUL listed	Yes
cUL certification	according to CSA C22.2 No. 182.3 (e-file number: E249137)
CSA certified	No
VDE certified	No
Product standard according to IEC	M8 according to IEC 61076-2-104
DNV-certified	No
Ecolab certified	No

UNITRONIC® SENSOR M8-M8

Article No.	Name	Base material of outer sheath, shortname	Number of cores	Length	Connector 1	Connector 2
22260060	AB-C4-M8MS-0,6PUR-M8FA	PUR	4	0.6 m	M 8; Plug; Straight; A-coded; Number of contacts: 4	M 8; Socket; Angled; A-coded; Number of contacts: 4
22260061	AB-C4-M8MS-1,0PUR-M8FA	PUR	4	1 m	M 8; Plug; Straight; A-coded; Number of contacts: 4	M 8; Socket; Angled; A-coded; Number of contacts: 4
22260062	AB-C4-M8MS-2,0PUR-M8FA	PUR	4	2 m	M 8; Plug; Straight; A-coded; Number of contacts: 4	M 8; Socket; Angled; A-coded; Number of contacts: 4
22260206	AB-C3-M8MS-0,3PUR-M8FS	PUR	3	0.3 m	M 8; Plug; Straight; A-coded; Number of contacts: 3	M 8; Socket; Straight; A-coded; Number of contacts: 3
22260207	AB-C3-M8MS-0,6PUR-M8FS	PUR	3	0.6 m	M 8; Plug; Straight; A-coded; Number of contacts: 3	M 8; Socket; Straight; A-coded; Number of contacts: 3
22260208	AB-C3-M8MS-1,0PUR-M8FS	PUR	3	1 m	M 8; Plug; Straight; A-coded; Number of contacts: 3	M 8; Socket; Straight; A-coded; Number of contacts: 3
22260209	AB-C3-M8MS-2,0PUR-M8FS	PUR	3	2 m	M 8; Plug; Straight; A-coded; Number of contacts: 3	M 8; Socket; Straight; A-coded; Number of contacts: 3
22260210	AB-C3-M8MS-0,3PUR-M8FA	PUR	3	0.3 m	M 8; Plug; Straight; A-coded; Number of contacts: 3	M 8; Socket; Angled; A-coded; Number of contacts: 3
22260211	AB-C3-M8MS-0,6PUR-M8FA	PUR	3	0.6 m	M 8; Plug; Straight; A-coded; Number of contacts: 3	M 8; Socket; Angled; A-coded; Number of contacts: 3
22260212	AB-C3-M8MS-1,0PUR-M8FA	PUR	3	1 m	M 8; Plug; Straight; A-coded; Number of contacts: 3	M 8; Socket; Angled; A-coded; Number of contacts: 3
22260213	AB-C3-M8MS-2,0PUR-M8FA	PUR	3	2 m	M 8; Plug; Straight; A-coded; Number of contacts: 3	M 8; Socket; Angled; A-coded; Number of contacts: 3
22260214	AB-C3-M8MS-0,3PUR-M8FA-2L	PUR	3	0.3 m	M 8; Plug; Straight; A-coded; Number of contacts: 3	M 8; Socket; Angled; A-coded; Number of contacts: 3; LED
22260215	AB-C3-M8MS-0,6PUR-M8FA-2L	PUR	3	0.6 m	M 8; Plug; Straight; A-coded; Number of contacts: 3	M 8; Socket; Angled; A-coded; Number of contacts: 3; LED
22260216	AB-C3-M8MS-1,0PUR-M8FA-2L	PUR	3	1 m	M 8; Plug; Straight; A-coded; Number of contacts: 3	M 8; Socket; Angled; A-coded; Number of contacts: 3; LED
22260217	AB-C3-M8MS-2,0PUR-M8FA-2L	PUR	3	2 m	M 8; Plug; Straight; A-coded; Number of contacts: 3	M 8; Socket; Angled; A-coded; Number of contacts: 3; LED

Article No.	Name	Base material of outer sheath, shortname	Number of cores	Length	Connector 1	Connector 2
22260313	AB-C4-M8MS-0,3PUR-M8FS	PUR	4	0.3 m	M 8; Plug; Straight; A-coded; Number of contacts: 4	M 8; Socket; Straight; A-coded; Number of contacts: 4
22260314	AB-C4-M8MS-0,6PUR-M8FS	PUR	4	0.6 m	M 8; Plug; Straight; A-coded; Number of contacts: 4	M 8; Socket; Straight; A-coded; Number of contacts: 4
22260315	AB-C4-M8MS-1,0PUR-M8FS	PUR	4	1 m	M 8; Plug; Straight; A-coded; Number of contacts: 4	M 8; Socket; Straight; A-coded; Number of contacts: 4
22260316	AB-C4-M8MS-2,0PUR-M8FS	PUR	4	2 m	M 8; Plug; Straight; A-coded; Number of contacts: 4	M 8; Socket; Straight; A-coded; Number of contacts: 4
22260923	AB-C4-M8MS-5,0PUR-M8FS	PUR	4	5 m	M 8; Plug; Straight; A-coded; Number of contacts: 4	M 8; Socket; Straight; A-coded; Number of contacts: 4
22260938	AB-C3-M8MS-5,0PUR-M8FS	PUR	3	5 m	M 8; Plug; Straight; A-coded; Number of contacts: 3	M 8; Socket; Straight; A-coded; Number of contacts: 3

V1.1