

---

**FLAT GROUND STRAP/PRESS. 1X25/M8/300MM****Article No.:** 4571137Grounding strap; 25 mm<sup>2</sup>; Total length: 300mm; M 8**Details****Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

**Remarks**

Trade product, not a LAPP product.

**Technical Data****General information**

Product type	Grounding strap
--------------	-----------------

---

---

Copper index	0.15 lb/pce
Delivery Unit	25
Industry segment	Lifts & Elevators

---

**Electrical parameters**

---

test voltage	2.5 kV
--------------	--------

---

**Product design**

---

Conductor material	Tin-plated Copper
Total length	11.811 in
Screw-in thread	M 8
EMC shielding	Yes
Connectable conductor cross section (mm <sup>2</sup> )	25 mm <sup>2</sup>

---

**Product features****Certifications and standards**

---

UL recognized	Yes
UL listed	No
cUR recognized	No
VDE certified	No

---

**Flat Ground Straps**

Article No.	Name	Screw-in thread	Total length	Connectable conductor cross section (mm <sup>2</sup> )	Delivery Unit
4571126	FLAT GROUND STRAP/TERMINALS 1X10/M6/200	M 6	7.874 in	10 mm <sup>2</sup>	25
4571127	FLAT GROUND STRAP/TERMINALS 1X16/M8/200	M 8	7.874 in	16 mm <sup>2</sup>	25
4571128	FLAT GROUND STRAP/TERMINALS 1X25/M8/200	M 8	7.874 in	25 mm <sup>2</sup>	25
4571129	FLAT GROUND STRAP/TERMINALS 1X10/M6/300	M 6	11.811 in	10 mm <sup>2</sup>	25
4571130	FLAT GROUND STRAP/TERMINALS 1X16/M8/300	M 8	11.811 in	16 mm <sup>2</sup>	25
4571131	FLAT GROUND STRAP/TERMINALS 1X25/M8/300	M 8	11.811 in	25 mm <sup>2</sup>	25
4571132	FLAT GROUND STRAP/PRESS. 1X10/M6/200MM	M 6	7.874 in	10 mm <sup>2</sup>	25
4571133	FLAT GROUND STRAP/PRESS. 1X16/M8/200MM	M 8	7.874 in	16 mm <sup>2</sup>	25
4571134	FLAT GROUND STRAP/PRESS. 1X25/M8/200MM	M 8	7.874 in	25 mm <sup>2</sup>	25
4571135	FLAT GROUND STRAP/PRESS. 1X10/M6/300MM	M 6	11.811 in	10 mm <sup>2</sup>	25
4571136	FLAT GROUND STRAP/PRESS. 1X16/M8/300MM	M 8	11.811 in	16 mm <sup>2</sup>	25
4571137	FLAT GROUND STRAP/PRESS. 1X25/M8/300MM	M 8	11.811 in	25 mm <sup>2</sup>	25
4571196	FLAT GROUND STRAP/TERMINAL 1X6/M6/200MM	M 6	7.874 in	6 mm <sup>2</sup>	25
4571197	FLAT GROUND STRAP/TERMINALS 1X6/M6/300MM	M 6	11.811 in	6 mm <sup>2</sup>	25
70399965	FLAT GROUND STRAP/PRESS. 1X16/M6/200MM	M 6	7.874 in	16 mm <sup>2</sup>	25
70399966	FLAT GROUND STRAP/PRESS. 1X16/M6/300MM	M 6	11.811 in	16 mm <sup>2</sup>	25
70399969	FLAT GROUND STRAP/PRESS. 1X25/M8/500MM	M 8	19.685 in	25 mm <sup>2</sup>	25

V1.1