

SKINDICHT® KUK PG 16/9 REDUCER

Article No.: 51730025

Reducer; Inner thread: PG 9; Outer thread: PG 16; Polyamide; light gray



CE



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

| | |
|------------------------|------------|
| Brand | SKINDICHT® |
| Product type | Reducer |
| Delivery with lock nut | No |
| Including o-ring | No |

| | |
|-------------------|----------------------|
| Type of packaging | Bag |
| Delivery Unit | 50 |
| Mounting method | in threaded borehole |

Electrical parameters

Product design

| | |
|---------------------------|------------|
| Glass-fibre reinforced | Yes |
| Cable gland design | Straight |
| Inner thread | PG 9 |
| Outer thread | PG 16 |
| Total length | 0.472 in |
| Overall width | 1.102 in |
| Thread type | PG |
| Thread size | PG 16 |
| Pitch of thread | 1,41 |
| Thread length | 0.354 in |
| Body material | Polyamide |
| Body material, short form | PA |
| Surface protection | Uncoated |
| Colour description | light gray |
| RAL color | RAL 7035 |

Product features

| | |
|------------------------------|--------|
| Suitable for EX-applications | No |
| Temperature (min.) | -40 °C |
| Max. temperatur | 100 °C |
| Flame-retardant | No |
| UV-resistant | No |
| Halogenfree | Yes |
| Oil resistant | Yes |

Certifications and standards

| | |
|------------------|-----|
| CE marking | Yes |
| UL recognized | No |
| UL listed | No |
| cUR recognized | No |
| cUL listed | No |
| CSA certified | No |
| VDE certified | No |
| GGVS certified | No |
| Ecolab certified | No |
| NSF certified | No |
| EHEDG certified | No |

SKINDICHT® KUK

| Article No. | Name | Outer thread | Inner thread | Colour description | Delivery Unit |
|-------------|-----------------------------------|--------------|--------------|--------------------|---------------|
| 51730020 | SKINDICHT® KUK PG 13.5/9 REDUCER | PG 13,5 | PG 9 | light gray | 50 |
| 51730025 | SKINDICHT® KUK PG 16/9 REDUCER | PG 16 | PG 9 | light gray | 50 |
| 51730030 | SKINDICHT® KUK PG 16/11 REDUCER | PG 16 | PG 11 | light gray | 50 |
| 51730035 | SKINDICHT® KUK PG 21/13.5 REDUCER | PG 21 | PG 13,5 | light gray | 50 |
| 51730090 | SKINDICHT® KUK PG 21/16 REDUCER | PG 21 | PG 16 | light gray | 50 |
| 51730100 | SKINDICHT® KUK PG 29/21 REDUCER | PG 29 | PG 21 | light gray | 25 |
| 51730110 | SKINDICHT® KUK PG 36/29 REDUCER | PG 36 | PG 29 | light gray | 25 |

V1.1