

**SKINDICHT® GMK PG 9 RAL 7035 LGY**

**Article No.:** 52000120

Lock nut; PG 9; Wrench width: 0.866in; light gray; Polystyrene; Halogen-free;



**Details**

**Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

**Remarks**

**Technical Data**

**General information**

Brand	SKINDICHT®
Product type	Lock nut
Type of packaging	Bag
Delivery Unit	100

## Electrical parameters

### Product design

Glass-fibre reinforced	No
Thickness	0.197 in
Thread type	PG
Thread size	PG 9
Pitch of thread	1,41
Hexagon corner dimensions	0.945 in
Wrench width	0.866 in
EMC shielding	No
Body material	Polystyrene
Body material, short form	PS
Surface protection	Uncoated
Colour description	light gray
RAL color	RAL 7035

### Product features

Suitable for EX-applications	No
Temperature (min.)	-20 °C
Max. temperatur	60 °C
Flame-retardant	No
UV-resistant	No
Halogenfree	Yes
Oil resistant	Yes
Impact proof	No

### Certifications and standards

CE marking	Yes
UL recognized	No
UL listed	No

---

cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

---

**SKINDICHT® GMK**

Article No.	Name	Thread size	Wrench width	Colour description	Delivery Unit
52000110	SKINDICHT® GMK PG 7 RAL 7035 LGY	PG 7	0.748 in	light gray	100
52000120	SKINDICHT® GMK PG 9 RAL 7035 LGY	PG 9	0.866 in	light gray	100
52000130	SKINDICHT® GMK PG 11 RAL 7035 LGY	PG 11	0.945 in	light gray	100
52000140	SKINDICHT® GMK PG 13.5 RAL 7035 LGY	PG 13,5	1.063 in	light gray	100
52000150	SKINDICHT® GMK PG 16 RAL 7035 LGY	PG 16	1.181 in	light gray	100
52000160	SKINDICHT® GMK PG 21 RAL 7035 LGY	PG 21	1.417 in	light gray	50
52000170	SKINDICHT® GMK PG 29 RAL 7035 LGY	PG 29	1.811 in	light gray	50
52000180	SKINDICHT® GMK PG 36 RAL 7035 LGY	PG 36	2.362 in	light gray	25
52000190	SKINDICHT® GMK PG 42 RAL 7035 LGY	PG 42	2.559 in	light gray	25
52000200	SKINDICHT® GMK PG 48 RAL 7035 LGY	PG 48	2.756 in	light gray	25

V1.1