

SKINDICHT® SNR PG 36/30 BEND PROTECTION

Article No.: 52002140

Sealing cone; Clear width: 1.181in; Chloroprene rubber; CR; black



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one PU.

Technical Data

General information

Brand	SKINDICHT®
Product type	Sealing cone

Type of packaging	Loose
Delivery Unit	25

Electrical parameters

Product design

Bending protection	Anti-kink sleeve
With bending protection	Yes
Cable gland design	Straight
Inner diameter	1.181 in
Outer diameter	1.772 in
Total length	3.819 in
Clear width	1.181 in
Thread size	PG 36
Seal type	Sealing cone
Material sealing	Chloroprene rubber
Colour description	black

Product features

Suitable for EX-applications	No
Temperature (min.)	-20 °C
Max. temperatur	80 °C
Flame-retardant	No
UV-resistant	Yes
Chemical resistant	Yes
Acid-resistant	No
Halogenfree	No
Oil resistant	Yes

Certifications and standards

CE marking	No
------------	----

Ecolab certified	No
------------------	----

SKINDICHT® SNR

Article No.	Name	Clear width	Delivery Unit
52001970	SKINDICHT® SNR PG 7/5 BEND PROTECTION	0.197 in	100
52001980	SKINDICHT® SNR PG 9/7 BEND PROTECTION	0.276 in	100
52001990	SKINDICHT® SNR PG 11/7 BEND PROTECTION	0.276 in	100
52002000	SKINDICHT® SNR PG 11/9 BEND PROTECTION	0.354 in	100
52002010	SKINDICHT® SNR PG 13/9 BEND PROTECTION	0.354 in	100
52002020	SKINDICHT® SNR PG 13/11 BEND PROTECTION	0.433 in	100
52002030	SKINDICHT® SNR PG 13/13 BEND PROTECTION	0.512 in	100
52002040	SKINDICHT® SNR PG 16/13 BEND PROTECTION	0.512 in	100
52002050	SKINDICHT® SNR PG 16/15 BEND PROTECTION	0.591 in	100
52002060	SKINDICHT® SNR PG 21/15 BEND PROTECTION	0.591 in	50
52002070	SKINDICHT® SNR PG 21/17 BEND PROTECTION	0.669 in	50
52002080	SKINDICHT® SNR PG 21/19 BEND PROTECTION	0.748 in	50
52002090	SKINDICHT® SNR PG 21/20 BEND PROTECTION	0.787 in	50
52002100	SKINDICHT® SNR PG 29/20 BEND PROTECTION	0.787 in	25
52002110	SKINDICHT® SNR PG 29/23 BEND PROTECTION	0.906 in	25
52002120	SKINDICHT® SNR PG 29/25 BEND PROTECTION	0.996 in	25
52002130	SKINDICHT® SNR PG 36/26 BEND PROTECTION	1.024 in	25
52002140	SKINDICHT® SNR PG 36/30 BEND PROTECTION	1.181 in	25
52002150	SKINDICHT® SNR PG 36/33 BEND PROTECTION	1.299 in	25
52002160	SKINDICHT® SNR PG 36/35 BEND PROTECTION	1.378 in	25
52002170	SKINDICHT® SNR PG 42/35 BEND PROTECTION	1.378 in	10
52002180	SKINDICHT® SNR PG 42/38 BEND PROTECTION	1.496 in	10
52002190	SKINDICHT® SNR PG 42/40 BEND PROTECTION	1.594 in	10

V1.1