

SKINDICHT® SNR PG 36/33 BEND PROTECTION

Article No.: 52002150

Sealing cone; Clear width: 1.299in; Chloroprene rubber; CR; black



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one PU.

Technical Data

General information

| | |
|--------------|--------------|
| Brand | SKINDICHT® |
| Product type | Sealing cone |

| | |
|-------------------|-------|
| Type of packaging | Loose |
| Delivery Unit | 25 |

Electrical parameters**Product design**

| | |
|-------------------------|--------------------|
| Bending protection | Anti-kink sleeve |
| With bending protection | Yes |
| Cable gland design | Straight |
| Inner diameter | 1.299 in |
| Outer diameter | 1.772 in |
| Total length | 3.819 in |
| Clear width | 1.299 in |
| Thread size | PG 36 |
| Seal type | Sealing cone |
| Material sealing | Chloroprene rubber |
| Colour description | black |

Product features

| | |
|------------------------------|--------|
| Suitable for EX-applications | No |
| Temperature (min.) | -20 °C |
| Max. temperatur | 80 °C |
| Flame-retardant | No |
| UV-resistant | Yes |
| Chemical resistant | Yes |
| Acid-resistant | No |
| Halogenfree | No |
| Oil resistant | Yes |

Certifications and standards

| | |
|------------|----|
| CE marking | No |
|------------|----|

| | |
|------------------|----|
| Ecolab certified | No |
|------------------|----|

SKINDICHT® SNR

| Article No. | Name | Clear width | Delivery Unit |
|-------------|---|-------------|---------------|
| 52001970 | SKINDICHT® SNR PG 7/5 BEND PROTECTION | 0.197 in | 100 |
| 52001980 | SKINDICHT® SNR PG 9/7 BEND PROTECTION | 0.276 in | 100 |
| 52001990 | SKINDICHT® SNR PG 11/7 BEND PROTECTION | 0.276 in | 100 |
| 52002000 | SKINDICHT® SNR PG 11/9 BEND PROTECTION | 0.354 in | 100 |
| 52002010 | SKINDICHT® SNR PG 13/9 BEND PROTECTION | 0.354 in | 100 |
| 52002020 | SKINDICHT® SNR PG 13/11 BEND PROTECTION | 0.433 in | 100 |
| 52002030 | SKINDICHT® SNR PG 13/13 BEND PROTECTION | 0.512 in | 100 |
| 52002040 | SKINDICHT® SNR PG 16/13 BEND PROTECTION | 0.512 in | 100 |
| 52002050 | SKINDICHT® SNR PG 16/15 BEND PROTECTION | 0.591 in | 100 |
| 52002060 | SKINDICHT® SNR PG 21/15 BEND PROTECTION | 0.591 in | 50 |
| 52002070 | SKINDICHT® SNR PG 21/17 BEND PROTECTION | 0.669 in | 50 |
| 52002080 | SKINDICHT® SNR PG 21/19 BEND PROTECTION | 0.748 in | 50 |
| 52002090 | SKINDICHT® SNR PG 21/20 BEND PROTECTION | 0.787 in | 50 |
| 52002100 | SKINDICHT® SNR PG 29/20 BEND PROTECTION | 0.787 in | 25 |
| 52002110 | SKINDICHT® SNR PG 29/23 BEND PROTECTION | 0.906 in | 25 |
| 52002120 | SKINDICHT® SNR PG 29/25 BEND PROTECTION | 0.996 in | 25 |
| 52002130 | SKINDICHT® SNR PG 36/26 BEND PROTECTION | 1.024 in | 25 |
| 52002140 | SKINDICHT® SNR PG 36/30 BEND PROTECTION | 1.181 in | 25 |
| 52002150 | SKINDICHT® SNR PG 36/33 BEND PROTECTION | 1.299 in | 25 |
| 52002160 | SKINDICHT® SNR PG 36/35 BEND PROTECTION | 1.378 in | 25 |
| 52002170 | SKINDICHT® SNR PG 42/35 BEND PROTECTION | 1.378 in | 10 |
| 52002180 | SKINDICHT® SNR PG 42/38 BEND PROTECTION | 1.496 in | 10 |
| 52002190 | SKINDICHT® SNR PG 42/40 BEND PROTECTION | 1.594 in | 10 |

V1.1