

SKINDICHT® WN-M 20X1.5 LGY WO. HOLE**Article No.:** 52020523

Bushing; Thread size: M 20; light gray; Polyethylene

**CE****Details****Notes**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Remarks**Technical Data****General information**

Brand	SKINDICHT®
Product type	Bushing
Delivery with lock nut	No
Including o-ring	No

Type of packaging	Bag
Delivery Unit	200
Mounting method	in threaded borehole

Electrical parameters

Product design

Glass-fibre reinforced	No
Total length	0.787 in
Overall width	0.945 in
Clear width	0.531 in
Thread type	Metric
Thread size	M 20
Pitch of thread	1,5
Thread length	0.472 in
Thread standard	DIN EN 60423
Wrench width	0.748 in
For min. cable outer diameter	0.315 in
For max. cable outer diameter	0.531 in
Body material	Polyethylene
Body material, short form	PET
Surface protection	Uncoated
Colour description	light gray
RAL color	RAL 7035

Product features

IP protection rating	IP 54
Suitable for EX-applications	No
Temperature (min.)	-30 °C
Max. temperatur	80 °C
Flame-retardant	No
UV-resistant	No

Halogenfree	Yes
Oil resistant	No

Certifications and standards

CE marking	Yes
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
For Ex zone gas	without
For Ex-zone dust	without
GGVS certified	No
DNV-certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

SKINDICHT® WN-M

Article No.	Name	Thread size	Clear width	Delivery Unit
52020513	SKINDICHT® WN-M 16X1.5 WO. HOLE	M 16	0.394 in	200
52020523	SKINDICHT® WN-M 20X1.5 LGY WO. HOLE	M 20	0.531 in	200
52020533	SKINDICHT® WN-M 25X1.5 WO. HOLE	M 25	0.63 in	100
52020543	SKINDICHT® WN-M 32X1.5 WO. HOLE	M 32	0.866 in	50
52020553	SKINDICHT® WN-M 40X1.5 WO. HOLE	M 40	0.945 in	50
52020563	SKINDICHT® WN-M 50X1.5 WO. HOLE	M 50	1.378 in	20
52020573	SKINDICHT® WN-M 63X1.5 WO. HOLE	M 63	1.693 in	10

V1.1