

SKINDICHT® WN-M 32X1.5 WO. HOLE

Article No.: 52020543

Bushing; Thread size: M 32; light gray; Polyethylene



Details

Notes

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Remarks

Technical Data

General information

| | |
|------------------------|------------|
| Brand | SKINDICHT® |
| Product type | Bushing |
| Delivery with lock nut | No |
| Including o-ring | No |

| | |
|-------------------|----------------------|
| Type of packaging | Bag |
| Delivery Unit | 50 |
| Mounting method | in threaded borehole |

Electrical parameters

Product design

| | |
|-------------------------------|--------------|
| Glass-fibre reinforced | No |
| Total length | 0.984 in |
| Overall width | 1.457 in |
| Clear width | 0.866 in |
| Thread type | Metric |
| Thread size | M 32 |
| Pitch of thread | 1,5 |
| Thread length | 0.551 in |
| Thread standard | DIN EN 60423 |
| Wrench width | 1.181 in |
| For min. cable outer diameter | 0.433 in |
| For max. cable outer diameter | 0.866 in |
| Body material | Polyethylene |
| Body material, short form | PET |
| Surface protection | Uncoated |
| Colour description | light gray |
| RAL color | RAL 7035 |

Product features

| | |
|------------------------------|--------|
| IP protection rating | IP 54 |
| Suitable for EX-applications | No |
| Temperature (min.) | -30 °C |
| Max. temperatur | 80 °C |
| Flame-retardant | No |
| UV-resistant | No |

| | |
|---------------|-----|
| Halogenfree | Yes |
| Oil resistant | No |

Certifications and standards

| | |
|------------------|---------|
| CE marking | Yes |
| UL recognized | No |
| UL listed | No |
| cUR recognized | No |
| cUL listed | No |
| CSA certified | No |
| VDE certified | No |
| For Ex zone gas | without |
| For Ex-zone dust | without |
| GGVS certified | No |
| DNV-certified | No |
| Ecolab certified | No |
| NSF certified | No |
| EHEDG certified | No |

SKINDICHT® WN-M

| Article No. | Name | Thread size | Clear width | Delivery Unit |
|-------------|-------------------------------------|-------------|-------------|---------------|
| 52020513 | SKINDICHT® WN-M 16X1.5 WO. HOLE | M 16 | 0.394 in | 200 |
| 52020523 | SKINDICHT® WN-M 20X1.5 LGY WO. HOLE | M 20 | 0.531 in | 200 |
| 52020533 | SKINDICHT® WN-M 25X1.5 WO. HOLE | M 25 | 0.63 in | 100 |
| 52020543 | SKINDICHT® WN-M 32X1.5 WO. HOLE | M 32 | 0.866 in | 50 |
| 52020553 | SKINDICHT® WN-M 40X1.5 WO. HOLE | M 40 | 0.945 in | 50 |
| 52020563 | SKINDICHT® WN-M 50X1.5 WO. HOLE | M 50 | 1.378 in | 20 |
| 52020573 | SKINDICHT® WN-M 63X1.5 WO. HOLE | M 63 | 1.693 in | 10 |

V1.1