

**SKINDICHT® ZS-XL PG 9**

**Article No.:** 52020940

Collar; PG 9; Wrench width: 0.669in; Brass Nickel-plated



**CE**



**Details**

**Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

**Remarks**

**Technical Data**

**General information**

Brand	SKINDICHT®
Product type	neck
Delivery with lock nut	No
Including o-ring	No

Type of packaging	Bag
Delivery Unit	100
Mounting method	in threaded borehole

### Electrical parameters

#### Product design

Glass-fibre reinforced	No
Cable gland design	Straight
Inner thread	PG 9
Outer thread	PG 9
Total length	1.004 in
Overall width	0.744 in
Clear width	0.492 in
Thread size	PG 9
Pitch of thread	1,41
Thread length	0.591 in
Wrench width	0.669 in
Body material	Brass
Body material, short form	CuZn
Surface protection	Nickel-plated

#### Product features

Suitable for EX-applications	No
Temperature (min.)	-60 °C
Max. temperatur	200 °C
Flame-retardant	Yes
UV-resistant	Yes
Halogenfree	Yes
Oil resistant	Yes

---

**Certifications and standards**

CE marking	Yes
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

**SKINDICHT® ZS/ZS-XL**

Article No.	Name	Thread size	Wrench width	Delivery Unit
52020930	SKINDICHT® ZS-XL PG 11	PG 11	0.787 in	100
52020940	SKINDICHT® ZS-XL PG 9	PG 9	0.669 in	100
52020950	SKINDICHT® ZS-XL PG 13.5	PG 13,5	0.866 in	100
52020960	SKINDICHT® ZS-XL PG 16	PG 16	0.945 in	50
52020970	SKINDICHT® ZS-XL PG 21	PG 21	1.181 in	50
52020980	SKINDICHT® ZS-XL PG 29	PG 29	1.575 in	25
52020990	SKINDICHT® ZS-XL PG 36	PG 36	1.969 in	10
52021000	SKINDICHT® ZS-XL PG 42	PG 42	2.244 in	10
52100010	SKINDICHT® ZS PG 7	PG 7	0.551 in	100
52100020	SKINDICHT® ZS PG 9	PG 9	0.669 in	100
52100030	SKINDICHT® ZS PG 11	PG 11	0.787 in	100
52100040	SKINDICHT® ZS PG13.5	PG 13,5	0.866 in	100
52100050	SKINDICHT® ZS PG 16	PG 16	0.945 in	50
52100060	SKINDICHT® ZS PG 21	PG 21	1.181 in	50
52100070	SKINDICHT® ZS PG 29	PG 29	1.575 in	25
52100080	SKINDICHT® ZS PG 36	PG 36	1.969 in	10
52100090	SKINDICHT® ZS PG 42	PG 42	2.244 in	10
52100100	SKINDICHT® ZS PG 48	PG 48	2.52 in	10

V1.1