

**SKINDICHT® SHV PG9/7 CONE SEAL CR**

**Article No.:** 52021140

Sealing cone; Clear width: 0.276in; Chloroprene rubber; CR; black



**Details**

**Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

**Remarks**

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one PU.

**Technical Data**

**General information**

Brand	SKINDICHT®
Product type	Sealing cone

---

Type of packaging	Loose
Delivery Unit	100

---

**Electrical parameters****Product design**

With bending protection	No
Cable gland design	Straight
Inner diameter	0.276 in
Outer diameter	0.543 in
Total length	0.583 in
Clear width	0.276 in
Thread size	PG 9
Seal type	Sealing cone
Material sealing	Chloroprene rubber
Colour description	black

---

**Product features**

Suitable for EX-applications	No
Temperature (min.)	-20 °C
Max. temperatur	80 °C
Flame-retardant	No
UV-resistant	Yes
Chemical resistant	Yes
Acid-resistant	No
Halogenfree	No
Oil resistant	Yes

---

**Certifications and standards**

CE marking	No
Ecolab certified	No

---

**SKINDICHT® SHV CR**

Article No.	Name	Clear width	Delivery Unit
52021120	SKINDICHT® SHV PG7/5 CONE SEAL CR	0.197 in	100
52021130	SKINDICHT® SHV PG9/6 CONE SEAL CR	0.236 in	100
52021140	SKINDICHT® SHV PG9/7 CONE SEAL CR	0.276 in	100
52021150	SKINDICHT® SHV PG11/7 CONE SEAL CR	0.276 in	100
52021160	SKINDICHT® SHV PG11/9 CONE SEAL CR	0.354 in	100
52021170	SKINDICHT® SHV PG13.5/11 CONE SEAL CR	0.433 in	100
52021180	SKINDICHT® SHV PG13.5/9 CONE SEAL CR	0.354 in	100
52021190	SKINDICHT® SHV PG16/11 CONE SEAL CR	0.433 in	50
52021200	SKINDICHT® SHV PG16/13 CONE SEAL CR	0.512 in	50
52021210	SKINDICHT® SHV PG16/15 CONE SEAL CR	0.591 in	50
52021220	SKINDICHT® SHV PG21/18 CONE SEAL CR	0.709 in	50
52021230	SKINDICHT® SHV PG21/20 CONE SEAL CR	0.787 in	50
52021240	SKINDICHT® SHV PG29/22 CONE SEAL CR	0.866 in	25
52021250	SKINDICHT® SHV PG29/24 CONE SEAL CR	0.945 in	25
52021260	SKINDICHT® SHV PG29/26 CONE SEAL CR	1.024 in	25
52024460	SKINDICHT® SHV PG21/16 CONE SEAL CR	0.63 in	50

V1.1