

SKINDICHT® SHV PG16/13 CONE SEAL CR

Article No.: 52021200

Sealing cone; Clear width: 0.512in; Chloroprene rubber; CR; black



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one PU.

Technical Data

General information

| | |
|--------------|--------------|
| Brand | SKINDICHT® |
| Product type | Sealing cone |

| | |
|-------------------|-------|
| Type of packaging | Loose |
| Delivery Unit | 50 |

Electrical parameters**Product design**

| | |
|-------------------------|--------------------|
| With bending protection | No |
| Cable gland design | Straight |
| Inner diameter | 0.512 in |
| Outer diameter | 0.827 in |
| Total length | 0.768 in |
| Clear width | 0.512 in |
| Thread size | PG 16 |
| Seal type | Sealing cone |
| Material sealing | Chloroprene rubber |
| Colour description | black |

Product features

| | |
|------------------------------|--------|
| Suitable for EX-applications | No |
| Temperature (min.) | -20 °C |
| Max. temperatur | 80 °C |
| Flame-retardant | No |
| UV-resistant | Yes |
| Chemical resistant | Yes |
| Acid-resistant | No |
| Halogenfree | No |
| Oil resistant | Yes |

Certifications and standards

| | |
|------------------|----|
| CE marking | No |
| Ecolab certified | No |

SKINDICHT® SHV CR

| Article No. | Name | Clear width | Delivery Unit |
|-------------|---------------------------------------|-------------|---------------|
| 52021120 | SKINDICHT® SHV PG7/5 CONE SEAL CR | 0.197 in | 100 |
| 52021130 | SKINDICHT® SHV PG9/6 CONE SEAL CR | 0.236 in | 100 |
| 52021140 | SKINDICHT® SHV PG9/7 CONE SEAL CR | 0.276 in | 100 |
| 52021150 | SKINDICHT® SHV PG11/7 CONE SEAL CR | 0.276 in | 100 |
| 52021160 | SKINDICHT® SHV PG11/9 CONE SEAL CR | 0.354 in | 100 |
| 52021170 | SKINDICHT® SHV PG13.5/11 CONE SEAL CR | 0.433 in | 100 |
| 52021180 | SKINDICHT® SHV PG13.5/9 CONE SEAL CR | 0.354 in | 100 |
| 52021190 | SKINDICHT® SHV PG16/11 CONE SEAL CR | 0.433 in | 50 |
| 52021200 | SKINDICHT® SHV PG16/13 CONE SEAL CR | 0.512 in | 50 |
| 52021210 | SKINDICHT® SHV PG16/15 CONE SEAL CR | 0.591 in | 50 |
| 52021220 | SKINDICHT® SHV PG21/18 CONE SEAL CR | 0.709 in | 50 |
| 52021230 | SKINDICHT® SHV PG21/20 CONE SEAL CR | 0.787 in | 50 |
| 52021240 | SKINDICHT® SHV PG29/22 CONE SEAL CR | 0.866 in | 25 |
| 52021250 | SKINDICHT® SHV PG29/24 CONE SEAL CR | 0.945 in | 25 |
| 52021260 | SKINDICHT® SHV PG29/26 CONE SEAL CR | 1.024 in | 25 |
| 52024460 | SKINDICHT® SHV PG21/16 CONE SEAL CR | 0.63 in | 50 |

V1.1