

SKINDICHT® SHV PG 21/18 CONE SEAL FKM**Article No.:** 52021268

Sealing cone; Clear width: 0.709in; Fluorinated rubber; FKM; red

**Details****Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one PU.

Technical Data**General information**

Brand	SKINDICHT®
Product type	Sealing cone

Type of packaging	Loose
Delivery Unit	50

Electrical parameters

Product design

With bending protection	No
Cable gland design	Straight
Inner diameter	0.709 in
Outer diameter	1.043 in
Total length	0.78 in
Clear width	0.709 in
Thread size	PG 21
Seal type	Sealing cone
Material sealing	Fluorinated rubber
Body material	Fluorinated rubber
Body material, short form	FKM
Colour description	red

Product features

Suitable for EX-applications	No
Temperature (min.)	-20 °C
Max. temperatur	200 °C
Flame-retardant	No
UV-resistant	No
Chemical resistant	Yes
Acid-resistant	No
Halogenfree	No
Oil resistant	Yes

Certifications and standards

CE marking	No
------------	----

Ecolab certified	No
------------------	----

SKINDICHT® SHV FKM

Article No.	Name	Clear width	Delivery Unit
52021146	SKINDICHT® SHV PG 9/6 CONE SEAL FKM	0.236 in	100
52021259	SKINDICHT® SHV PG 7/5 CONE SEAL FKM	0.197 in	100
52021261	SKINDICHT® SHV PG 9/7 CONE SEAL FKM	0.276 in	100
52021262	SKINDICHT® SHV PG 11/7 CONE SEAL FKM	0.276 in	100
52021263	SKINDICHT® SHV PG 11/9 CONE SEAL FKM	0.354 in	100
52021265	SKINDICHT® SHV PG 16/13 CONE SEAL FKM	0.512 in	50
52021266	SKINDICHT® SHV PG 21/20 CONE SEAL FKM	0.787 in	50
52021267	SKINDICHT® SHV PG 29/22 CONE SEAL FKM	0.866 in	50
52021268	SKINDICHT® SHV PG 21/18 CONE SEAL FKM	0.709 in	50
52021269	SKINDICHT® SHV PG 16/15 CONE SEAL FKM	0.591 in	50
52021271	SKINDICHT® SHV PG 13.5/9 CONE SEAL FKM	0.354 in	100
52021272	SKINDICHT® SHV PG13.5/11 CONE SEAL FKM	0.433 in	100

V1.1