

**SILVYN® EE-K 17 GY**

**Article No.:** 52023360

End sleeve; Nominal size: 17; Polypropylene; gray



**CE**



**Details**

**Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

**Remarks**

**Technical Data**

**General information**

Brand	SILVYN®
Product type	End sleeve
Delivery with lock nut	No
Including o-ring	No

---

Type of packaging	Bag
Delivery Unit	50
Mounting method	screw

---

**Electrical parameters****Product design**

suitable for protective conduit size	17
With bending protection	No
Inner diameter	0.453 in
Clear width	0.453 in
Nominal size	17 "
Body material	Polypropylene
Body material, short form	PP
Colour description	gray

---

**Product features**

Suitable for EX-applications	No
Flame-retardant	Yes
Flame retardance according to	UL 94 HB
UV-resistant	No
Chemical resistant	Yes
Acid-resistant	Yes
Halogenfree	Yes
Oil resistant	Yes
Strain relief	No

---

**Certifications and standards**

CE marking	Yes
UL recognized	No
UL listed	No

---

---

cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

---

**SILVYN® EE-K**

Article No.	Name	Nominal size	Delivery Unit
52023340	SILVYN® EE-K 10 GY	10 "	50
52023350	SILVYN® EE-K 14 GY	14 "	50
52023360	SILVYN® EE-K 17 GY	17 "	50
52023370	SILVYN® EE-K 19 GY	19 "	50
52023380	SILVYN® EE-K 21 GY	21 "	50
52023390	SILVYN® EE-K 27 GY	27 "	25
52023400	SILVYN® EE-K 36 GY	36 "	25
52023410	SILVYN® EE-K 45 GY	45 "	20
52023430	SILVYN® EE-K 56 GY	56 "	10

V1.1