

SKINDICHT® RWV PG 29 W.OUT E+D**Article No.:** 52024015

Angled cable gland; PG 29; Zinc alloy Nickel-plated; Halogen-free; 90° angle;

**CE****Details****Application**

- Machine and equipment manufacturing
- Plant engineering

Notes

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Remarks**Technical Data****General information**

Brand

SKINDICHT®

Product type	Angled cable gland
Scope of delivery	including O-ring
Delivery with lock nut	No
Including o-ring	Yes
Type of packaging	Bag
Delivery Unit	10
Mounting method	in threaded borehole

Electrical parameters

Product design

For armored cables	No
Glass-fibre reinforced	No
Number of cable entries	1 pc.
With bending protection	No
Cable gland design	90° angle
Clear width	1.26 in
Thread type	PG
Thread size	PG 29
Pitch of thread	1,588
Thread length	0.354 in
Spanner size 1	1.614 in
Wrench size 2	1.457 in
Hexagon corner dimensions	1.772 in
Wrench width	1.614 in
EMC shielding	No
Seal type	O-ring
Thread-side sealing element	O-ring
Material o-ring	Acrylonitrile butadiene rubber
O-ring material, short form	NBR
Body material	Zinc alloy
Surface protection	Nickel-plated
Colour description	metal

Product features

Suitable for EX-applications	No
Temperature (min.)	-20 °C
Max. temperatur	100 °C
Flame-retardant	Yes
UV-resistant	Yes
Halogenfree	Yes
Oil resistant	Yes
Impact proof	Yes
Strain relief	No

Certifications and standards

CE marking	Yes
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
For Ex zone gas	without
For Ex-zone dust	without
GGVS certified	No
DNV-certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

SKINDICHT® RWV without E+D

Article No.	Name	Thread size	Thread length	Spanner size 1	Delivery Unit
52023970	SKINDICHT® RWV PG 9 W.OUT E+D	PG 9	0.264 in	0.709 in	25
52023980	SKINDICHT® RWV PG 11 W.OUT E+D	PG 11	0.276 in	0.827 in	25
52023990	SKINDICHT® RWV PG 13.5 W.OUT E+D	PG 13,5	0.295 in	0.906 in	25
52024000	SKINDICHT® RWV PG 16 W.OUT E+D	PG 16	0.315 in	1.024 in	10
52024010	SKINDICHT® RWV PG 21 W.OUT E+D	PG 21	0.315 in	1.26 in	10
52024015	SKINDICHT® RWV PG 29 W.OUT E+D	PG 29	0.354 in	1.614 in	10
52024020	SKINDICHT® RWV PG 7 W.OUT E+D	PG 7	0.224 in	0.591 in	25

V1.1