

SKINDICHT® SHV-FKM PG 21/21/20

Article No.: 52024967

Cable gland; PG 21; Clamping range (min./max.): 0.689 - 0.78 in; Wrench width 1: 1.181; Brass Nickel-plated; IP 68 - 10 g/cm²;



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	SKINDICHT®
Product type	Cable gland
Delivery with lock nut	No
Including o-ring	Yes

Type of packaging	Bag
Delivery Unit	25
Mounting method	in threaded borehole

Electrical parameters

Product design

For armored cables	No
Glass-fibre reinforced	No
Number of cable entries	1 pc.
With bending protection	No
Cable gland design	Straight
Total length	1.496 in
Thread type	PG
Thread size	PG 21
Thread length	0.276 in
Spanner size 1	1.181 in
Wrench size 2	1.181 in
Hexagon corner dimensions	1.319 in
Clamping range min.	0.689 in
Clamping range max.	0.78 in
EMC shielding	No
Seal type	Sealing cone
Thread-side sealing element	O-ring
Cable-side sealing element	Sealing cone
Material sealing	Fluorinated rubber
Body material	Brass
Body material, short form	CuZn
Surface protection	Nickel-plated
Colour description	metal

Product features

IP protection rating	IP 68 - 10 g/cm ²
Suitable for EX-applications	No
Temperature static min.	-20 °C
Max. static temperature	200 °C
Temperature (min.)	-20 °C
Max. temperatur	200 °C
Flame-retardant	No
UV-resistant	No
Halogenfree	No
Oil resistant	Yes
Impact proof	Yes
Strain relief	Yes

Certifications and standards

CE marking	Yes
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
For Ex zone gas	without
For Ex-zone dust	without
GGVS certified	No
DNV-certified	No
Tested for fire protection for railway vehicles	No
Ecolab certified	No
NSF certified	No
FDA certified	No
EHEDG certified	No

SKINDICHT® SHV FKM

Article No.	Name	Thread size	Thread length	Clamping range min.	Clamping range max.	Spanner size 1	Delivery Unit
52024935	SKINDICHT® SHV-FKM PG 9/9/7	PG 9	0.236 in	0.189 in	0.228 in	0.669 in	50
52024937	SKINDICHT® SHV-FKM PG 11/11/9	PG 11	0.236 in	0.268 in	0.346 in	0.787 in	25
52024962	SKINDICHT® SHV-FKM PG 13/13/11	PG 13,5	0.256 in	0.335 in	0.425 in	0.866 in	25
52024967	SKINDICHT® SHV-FKM PG 21/21/20	PG 21	0.276 in	0.689 in	0.78 in	1.181 in	25
52024968	SKINDICHT® SHV-FKM PG 13/11/9	PG 13,5	0.256 in	0.268 in	0.346 in	0.866 in	25
52024969	SKINDICHT® SHV-FKM PG 13/11/11	PG 13,5	0.256 in	0.335 in	0.425 in	0.866 in	25
54000015	SKINDICHT® SHV-FKM PG 9/9/6	PG 9	0.236 in	0.189 in	0.228 in	0.669 in	50

V1.1