

**CABLE WEDGE CLAMPS DKK 18****Article No.:** 52026010

Cable wedge clamp; Cable diameter: 0.591in - 0.709in; Number of cables: 2;

**Details****Notes**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Trade product, not a LAPP product.

**Remarks**

Trade product, not a LAPP product.

**Technical Data****General information**

Product type	Cable wedge clamp
Scope of delivery	including screws including impact anchor including lock washer
Delivery Unit	1

**Electrical parameters****Product design**

number of cables	2
Total length	4.921 in
Overall width	3.346 in
Overall height	4.724 in
For min. cable outer diameter	0.591 in
For max. cable outer diameter	0.709 in

**Product features**

Halogenfree	No
Clamping force (max.)	800 N

**Certifications and standards**

---

**DKK double clamp**

Article No.	Name	For min. cable outer diameter	For max. cable outer diameter	number of cables	Delivery Unit
52026000	CABLE WEDGE CLAMPS EKK 18	0.591 in	0.709 in	1	1
52026010	CABLE WEDGE CLAMPS DKK 18	0.591 in	0.709 in	2	1

V1.1