

SKINDICHT® SM-M 25X1.5 INOX

Article No.: 52032635

Lock nut; M 25; Stainless steel Uncoated



CE



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	SKINDICHT®
Product type	Lock nut
Type of packaging	Bag

Delivery Unit	10
Industry segment	Agricultural & Farm Machinery

Electrical parameters

Product design

Glass-fibre reinforced	No
Thickness	0.138 in
Thread type	Metric
Thread size	M 25
Pitch of thread	1,5
Thread standard	DIN EN 60423
Hexagon corner dimensions	1.299 in
Wrench width	1.181 in
EMC shielding	No
Body material	Stainless steel
Surface protection	Uncoated
Colour description	metal

Product features

Suitable for EX-applications	No
Temperature (min.)	-60 °C
Max. temperatur	200 °C
Flame-retardant	Yes
UV-resistant	Yes
Chemical resistant	Yes
Halogenfree	Yes
Oil resistant	Yes
Impact proof	Yes

Certifications and standards

CE marking	Yes
EAC certified	Not required
EAC certification number	Отказное письмо № 43
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
Tested for fire protection for railway vehicles	No
Ecolab certified	No
NSF certified	No
FDA certified	No
EHEDG certified	No

SKINDICHT® SM-M INOX

Article No.	Name	Thread size	Wrench width	Delivery Unit
52032585	SKINDICHT® SM-M 12X1.5 INOX	M 12	0.591 in	10
52032615	SKINDICHT® SM-M 16X1.5 INOX	M 16	0.748 in	10
52032625	SKINDICHT® SM-M 20X1.5 INOX	M 20	0.945 in	10
52032635	SKINDICHT® SM-M 25X1.5 INOX	M 25	1.181 in	10
52032645	SKINDICHT® SM-M 32X1.5 INOX	M 32	1.417 in	10
52032655	SKINDICHT® SM-M 40X1.5 INOX	M 40	1.811 in	10
52032665	SKINDICHT® SM-M 50X1.5 INOX	M 50	2.165 in	10
52032675	SKINDICHT® SM-M 63X1.5 INOX	M 63	2.756 in	10

V1.1