

SKINDICHT® SM-M 50X1.5 INOX

Article No.: 52032665

Lock nut; M 50; Stainless steel Uncoated



CE



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

| | |
|-------------------|------------|
| Brand | SKINDICHT® |
| Product type | Lock nut |
| Type of packaging | Bag |

| | |
|------------------|-------------------------------|
| Delivery Unit | 10 |
| Industry segment | Agricultural & Farm Machinery |

Electrical parameters

Product design

| | |
|---------------------------|-----------------|
| Glass-fibre reinforced | No |
| Thickness | 0.197 in |
| Thread type | Metric |
| Thread size | M 50 |
| Pitch of thread | 1,5 |
| Thread standard | DIN EN 60423 |
| Hexagon corner dimensions | 2.362 in |
| Wrench width | 2.165 in |
| EMC shielding | No |
| Body material | Stainless steel |
| Surface protection | Uncoated |
| Colour description | metal |

Product features

| | |
|------------------------------|--------|
| Suitable for EX-applications | No |
| Temperature (min.) | -60 °C |
| Max. temperatur | 200 °C |
| Flame-retardant | Yes |
| UV-resistant | Yes |
| Chemical resistant | Yes |
| Halogenfree | Yes |
| Oil resistant | Yes |
| Impact proof | Yes |

Certifications and standards

| | |
|---|----------------------|
| CE marking | Yes |
| EAC certified | Not required |
| EAC certification number | Отказное письмо № 43 |
| UL recognized | No |
| UL listed | No |
| cUR recognized | No |
| cUL listed | No |
| CSA certified | No |
| VDE certified | No |
| GGVS certified | No |
| Tested for fire protection for railway vehicles | No |
| Ecolab certified | No |
| NSF certified | No |
| FDA certified | No |
| EHEDG certified | No |

SKINDICHT® SM-M INOX

| Article No. | Name | Thread size | Wrench width | Delivery Unit |
|-------------|-----------------------------|-------------|--------------|---------------|
| 52032585 | SKINDICHT® SM-M 12X1.5 INOX | M 12 | 0.591 in | 10 |
| 52032615 | SKINDICHT® SM-M 16X1.5 INOX | M 16 | 0.748 in | 10 |
| 52032625 | SKINDICHT® SM-M 20X1.5 INOX | M 20 | 0.945 in | 10 |
| 52032635 | SKINDICHT® SM-M 25X1.5 INOX | M 25 | 1.181 in | 10 |
| 52032645 | SKINDICHT® SM-M 32X1.5 INOX | M 32 | 1.417 in | 10 |
| 52032655 | SKINDICHT® SM-M 40X1.5 INOX | M 40 | 1.811 in | 10 |
| 52032665 | SKINDICHT® SM-M 50X1.5 INOX | M 50 | 2.165 in | 10 |
| 52032675 | SKINDICHT® SM-M 63X1.5 INOX | M 63 | 2.756 in | 10 |

V1.1