

SKINDICHT® EKU-M 12X1.5/16X1.5 LGY

Article No.: 52100300

Enlarger; Inner thread: M 16; Outer thread: M 12; Polyamide; light gray



CE



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

| | |
|------------------------|------------|
| Brand | SKINDICHT® |
| Product type | Enlarger |
| Delivery with lock nut | No |
| Including o-ring | No |

| | |
|-------------------|----------------------|
| Type of packaging | Bag |
| Delivery Unit | 100 |
| Mounting method | in threaded borehole |

Electrical parameters**Product design**

| | |
|---------------------------|--------------|
| Glass-fibre reinforced | Yes |
| With bending protection | No |
| Cable gland design | Straight |
| Inner thread | M 16 |
| Outer thread | M 12 |
| Inner diameter | 0.236 in |
| Outer diameter | 0.866 in |
| Total length | 1.063 in |
| Clear width | 0.236 in |
| Thread size | M 12 |
| Pitch of thread | 1,5 |
| Thread length | 0.354 in |
| Thread standard | DIN EN 60423 |
| Spanner size 1 | 0.787 in |
| Hexagon corner dimensions | 0.866 in |
| EMC shielding | No |
| Body material | Polyamide |
| Body material, short form | PA |
| Surface protection | Uncoated |
| Colour description | light gray |
| RAL color | RAL 7035 |

Product features

| | |
|------------------------------|--------|
| Suitable for EX-applications | No |
| Temperature (min.) | -40 °C |

| | |
|--------------------|--------|
| Max. temperatur | 100 °C |
| Flame-retardant | No |
| UV-resistant | No |
| Chemical resistant | Yes |
| Acid-resistant | No |
| Halogenfree | Yes |
| Oil resistant | Yes |

Certifications and standards

| | |
|---|-----|
| CE marking | Yes |
| UL recognized | No |
| UL listed | No |
| cUR recognized | No |
| cUL listed | No |
| CSA certified | No |
| VDE certified | No |
| GGVS certified | No |
| Tested for fire protection for railway vehicles | No |
| Ecolab certified | No |
| NSF certified | No |
| FDA certified | No |
| EHEDG certified | No |

SKINDICHT® EKU-M

| Article No. | Name | Outer thread | Inner thread | Colour description | Delivery Unit |
|-------------|------------------------------------|--------------|--------------|--------------------|---------------|
| 52100300 | SKINDICHT® EKU-M 12X1.5/16X1.5 LGY | M 12 | M 16 | light gray | 100 |
| 52100301 | SKINDICHT® EKU-M 16X1.5/20X1.5 LGY | M 16 | M 20 | light gray | 100 |
| 52100302 | SKINDICHT® EKU-M 20X1.5/25X1.5 LGY | M 20 | M 25 | light gray | 100 |
| 52100303 | SKINDICHT® EKU-M 25X1.5/32X1.5 LGY | M 25 | M 32 | light gray | 50 |
| 52100304 | SKINDICHT® EKU-M 32X1.5/40X1.5 LGY | M 32 | M 40 | light gray | 25 |
| 52100305 | SKINDICHT® EKU-M 40X1.5/50X1.5 LGY | M 40 | M 50 | light gray | 10 |
| 52100306 | SKINDICHT® EKU-M 50X1.5/63X1.5 LGY | M 50 | M 63 | light gray | 10 |
| 52100308 | SKINDICHT® EKU-M 12X1.5/16X1.5 BK | M 12 | M 16 | black | 100 |
| 52100309 | SKINDICHT® EKU-M 16X1.5/20X1.5 BK | M 16 | M 20 | black | 100 |
| 52100310 | SKINDICHT® EKU-M 20X1.5/25X1.5 BK | M 20 | M 25 | black | 100 |
| 52100311 | SKINDICHT® EKU-M 25X1.5/32X1.5 BK | M 25 | M 32 | black | 50 |
| 52100312 | SKINDICHT® EKU-M 32X1.5/40X1.5 BK | M 32 | M 40 | black | 25 |
| 52100313 | SKINDICHT® EKU-M 40X1.5/50X1.5 BK | M 40 | M 50 | black | 10 |
| 52100314 | SKINDICHT® EKU-M 50X1.5/63X1.5 BK | M 50 | M 63 | black | 10 |

V1.1