

SKINDICHT® EKU-M 16X1.5/20X1.5 LGY

Article No.: 52100301

Enlarger; Inner thread: M 20; Outer thread: M 16; Polyamide; light gray



CE



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	SKINDICHT®
Product type	Enlarger
Delivery with lock nut	No
Including o-ring	No

Type of packaging	Bag
Delivery Unit	100
Mounting method	in threaded borehole

Electrical parameters

Product design

Glass-fibre reinforced	Yes
With bending protection	No
Cable gland design	Straight
Inner thread	M 20
Outer thread	M 16
Inner diameter	0.394 in
Outer diameter	1.063 in
Total length	1.063 in
Clear width	0.394 in
Thread size	M 16
Pitch of thread	1,5
Thread length	0.354 in
Thread standard	DIN EN 60423
Spanner size 1	0.945 in
Hexagon corner dimensions	1.063 in
EMC shielding	No
Body material	Polyamide
Body material, short form	PA
Surface protection	Uncoated
Colour description	light gray
RAL color	RAL 7035

Product features

Suitable for EX-applications	No
Temperature (min.)	-40 °C

Max. temperatur	100 °C
Flame-retardant	No
UV-resistant	No
Chemical resistant	Yes
Acid-resistant	No
Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

CE marking	Yes
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
Tested for fire protection for railway vehicles	No
Ecolab certified	No
NSF certified	No
FDA certified	No
EHEDG certified	No

SKINDICHT® EKU-M

Article No.	Name	Outer thread	Inner thread	Colour description	Delivery Unit
52100300	SKINDICHT® EKU-M 12X1.5/16X1.5 LGY	M 12	M 16	light gray	100
52100301	SKINDICHT® EKU-M 16X1.5/20X1.5 LGY	M 16	M 20	light gray	100
52100302	SKINDICHT® EKU-M 20X1.5/25X1.5 LGY	M 20	M 25	light gray	100
52100303	SKINDICHT® EKU-M 25X1.5/32X1.5 LGY	M 25	M 32	light gray	50
52100304	SKINDICHT® EKU-M 32X1.5/40X1.5 LGY	M 32	M 40	light gray	25
52100305	SKINDICHT® EKU-M 40X1.5/50X1.5 LGY	M 40	M 50	light gray	10
52100306	SKINDICHT® EKU-M 50X1.5/63X1.5 LGY	M 50	M 63	light gray	10
52100308	SKINDICHT® EKU-M 12X1.5/16X1.5 BK	M 12	M 16	black	100
52100309	SKINDICHT® EKU-M 16X1.5/20X1.5 BK	M 16	M 20	black	100
52100310	SKINDICHT® EKU-M 20X1.5/25X1.5 BK	M 20	M 25	black	100
52100311	SKINDICHT® EKU-M 25X1.5/32X1.5 BK	M 25	M 32	black	50
52100312	SKINDICHT® EKU-M 32X1.5/40X1.5 BK	M 32	M 40	black	25
52100313	SKINDICHT® EKU-M 40X1.5/50X1.5 BK	M 40	M 50	black	10
52100314	SKINDICHT® EKU-M 50X1.5/63X1.5 BK	M 50	M 63	black	10

V1.1