

**SKINDICHT® SM NPT 3/4IN INOX**

**Article No.:** 52103510

Lock nut; NPT 3/4"; Stainless steel Uncoated



**CE**



**Details**

**Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

**Remarks**

**Technical Data**

**General information**

Brand	SKINDICHT®
Product type	Lock nut
Type of packaging	Bag
Delivery Unit	50

### Electrical parameters

#### Product design

Glass-fibre reinforced	No
Thickness	0.177 in
Thread type	NPT
Thread size	NPT 3/4"
Pitch of thread	1,81
Hexagon corner dimensions	1.378 in
Wrench width	1.26 in
EMC shielding	No
Body material	Stainless steel
Surface protection	Uncoated
Colour description	metal

#### Product features

Suitable for EX-applications	No
Temperature (min.)	-60 °C
Max. temperatur	200 °C
Flame-retardant	Yes
UV-resistant	Yes
Chemical resistant	Yes
Acid-resistant	Yes
corrosion resistant	Yes
Halogenfree	Yes
Oil resistant	Yes
Impact proof	Yes

#### Certifications and standards

CE marking	Yes
EAC certified	Not required

---

EAC certification number	Отказное письмо № 43
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

---

---

**SKINDICHT® SM-NPT INOX**

Article No.	Name	Thread size	Wrench width	Delivery Unit
52103500	SKINDICHT® SM NPT 1/2IN INOX	NPT 1/2"	1.063 in	50
52103510	SKINDICHT® SM NPT 3/4IN INOX	NPT 3/4"	1.26 in	50
52103520	SKINDICHT® SM NPT 1IN INOX	NPT 1"	1.496 in	25
52103530	SKINDICHT® SM NPT 1 1/4IN INOX	NPT 1 1/4"	1.89 in	10

V1.1