

SKINDICHT® SM NPT 1 1/4IN INOX

Article No.: 52103530

Lock nut; NPT 1 1/4"; Stainless steel Uncoated



CE



Details

Notes

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Remarks

Technical Data

General information

| | |
|-------------------|------------|
| Brand | SKINDICHT® |
| Product type | Lock nut |
| Type of packaging | Bag |
| Delivery Unit | 10 |

Electrical parameters

Product design

| | |
|---------------------------|-----------------|
| Glass-fibre reinforced | No |
| Thickness | 0.256 in |
| Thread type | NPT |
| Thread size | NPT 1 1/4" |
| Pitch of thread | 2,21 |
| Hexagon corner dimensions | 2.087 in |
| Wrench width | 1.89 in |
| EMC shielding | No |
| Body material | Stainless steel |
| Surface protection | Uncoated |
| Colour description | metal |

Product features

| | |
|------------------------------|--------|
| Suitable for EX-applications | No |
| Temperature (min.) | -60 °C |
| Max. temperatur | 200 °C |
| Flame-retardant | Yes |
| UV-resistant | Yes |
| Chemical resistant | Yes |
| Acid-resistant | Yes |
| corrosion resistant | Yes |
| Halogenfree | Yes |
| Oil resistant | Yes |
| Impact proof | Yes |

Certifications and standards

| | |
|---------------|--------------|
| CE marking | Yes |
| EAC certified | Not required |

| | |
|--------------------------|----------------------|
| EAC certification number | Отказное письмо № 43 |
| UL recognized | No |
| UL listed | No |
| cUR recognized | No |
| cUL listed | No |
| CSA certified | No |
| VDE certified | No |
| GGVS certified | No |
| Ecolab certified | No |
| NSF certified | No |
| EHEDG certified | No |

SKINDICHT® SM-NPT INOX

| Article No. | Name | Thread size | Wrench width | Delivery Unit |
|-------------|--------------------------------|-------------|--------------|---------------|
| 52103500 | SKINDICHT® SM NPT 1/2IN INOX | NPT 1/2" | 1.063 in | 50 |
| 52103510 | SKINDICHT® SM NPT 3/4IN INOX | NPT 3/4" | 1.26 in | 50 |
| 52103520 | SKINDICHT® SM NPT 1IN INOX | NPT 1" | 1.496 in | 25 |
| 52103530 | SKINDICHT® SM NPT 1 1/4IN INOX | NPT 1 1/4" | 1.89 in | 10 |

V1.1