

SKINDICHT® SM NPT 1 1/2IN

Article No.: 52103580

Lock nut; NPT 1 1/2"; Wrench width: 2.165in; Brass Nickel-plated



CE



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	SKINDICHT®
Product type	Lock nut
Type of packaging	Bag
Delivery Unit	10

Electrical parameters**Product design**

Glass-fibre reinforced	No
Thickness	0.276 in
Thread type	NPT
Thread size	NPT 1 1/2"
Pitch of thread	2,21
Hexagon corner dimensions	2.402 in
Wrench width	2.165 in
EMC shielding	No
Body material	Brass
Body material, short form	CuZn
Surface protection	Nickel-plated
Colour description	metal

Product features

Suitable for EX-applications	No
Temperature (min.)	-60 °C
Max. temperatur	200 °C
Flame-retardant	Yes
UV-resistant	Yes
Halogenfree	Yes
Oil resistant	Yes
Impact proof	Yes

Certifications and standards

CE marking	Yes
EAC certified	Not required
EAC certification number	Отказное письмо № 43
UL recognized	No

UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

SKINDICHT® SM-NPT

Article No.	Name	Thread size	Wrench width	Delivery Unit
52103540	SKINDICHT® SM NPT 1/2IN	NPT 1/2"	1.063 in	50
52103550	SKINDICHT® SM NPT 3/4IN	NPT 3/4"	1.26 in	20
52103560	SKINDICHT® SM NPT 1IN	NPT 1"	1.496 in	20
52103570	SKINDICHT® SM NPT 1 1/4IN	NPT 1 1/4"	1.89 in	20
52103580	SKINDICHT® SM NPT 1 1/2IN	NPT 1 1/2"	2.165 in	10
52103590	SKINDICHT® SM NPT 2IN	NPT 2"	2.677 in	10

V1.1