

SKINDICHT® ZSE-M 20X1.5/21

Article No.: 52104050

Adapter; Inner thread: PG 21; Outer thread: M 20; Brass Nickel-plated



CE



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	SKINDICHT®
Product type	Adapter
Delivery with lock nut	No
Including o-ring	No

Type of packaging	Bag
Delivery Unit	50
Mounting method	in threaded borehole

Electrical parameters**Product design**

Cable gland design	Straight
Inner thread	PG 21
Outer thread	M 20
Thread size	M 20
Pitch of thread	1,5
Thread standard	DIN EN 60423
Body material	Brass
Body material, short form	CuZn
Surface protection	Nickel-plated

Product features

Suitable for EX-applications	No
Temperature (min.)	-60 °C
Max. temperatur	200 °C
Flame-retardant	Yes
UV-resistant	Yes
Chemical resistant	Yes
Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

CE marking	Yes
UL recognized	No
UL listed	No

cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
Ecolab certified	No
NSF certified	No
FDA certified	No
EHEDG certified	No

SKINDICHT® ZSE-M

Article No.	Name	Outer thread	Inner thread	Delivery Unit
52104050	SKINDICHT® ZSE-M 20X1.5/21	M 20	PG 21	50
52106000	SKINDICHT® ZSE-M 12X1.5/7	M 12	PG 7	100
52106010	SKINDICHT® ZSE-M 16X1.5/9	M 16	PG 9	100
52106020	SKINDICHT® ZSE-M 20X1.5/11	M 20	PG 11	100
52106030	SKINDICHT® ZSE-M 20X1.5/13.5	M 20	PG 13,5	100
52106035	SKINDICHT® ZSE-M-XL 20X1.5/13.5	M 20	PG 13,5	100
52106040	SKINDICHT® ZSE-M 20X1.5/16	M 20	PG 16	50
52106045	SKINDICHT® ZSE-M-XL 20X1.5/16	M 20	PG 16	50
52106050	SKINDICHT® ZSE-M 25X1.5/21	M 25	PG 21	50
52106055	SKINDICHT® ZSE-M-XL 25X1.5/21	M 25	PG 21	50
52106060	SKINDICHT® ZSE-M 32X1.5/29	M 32	PG 29	25
52106065	SKINDICHT® ZSE-M-XL 32X1.5/29	M 32	PG 29	25

V1.1