

SKINDICHT® KU-M 40X1.5/25X1.5 LGY

Article No.: 52104481

Reducer; Inner thread: M 25; Outer thread: M 40; Polyamide; light gray



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	SKINDICHT®
Product type	Reducer
Delivery with lock nut	No
Including o-ring	No

Type of packaging	Bag
Delivery Unit	25
Mounting method	in threaded borehole
Industry segment	Intralogistics & Material handling

Electrical parameters

Product design

Glass-fibre reinforced	Yes
Cable gland design	Straight
Inner thread	M 25
Outer thread	M 40
Total length	0.748 in
Overall width	2.008 in
Thread type	Metric
Thread size	M 40
Pitch of thread	1,5
Thread length	0.472 in
Thread standard	DIN EN 60423
Wrench width	1.811 in
Body material	Polyamide
Body material, short form	PA
Surface protection	Uncoated
Colour description	light gray
RAL color	RAL 7035

Product features

Suitable for EX-applications	No
Temperature (min.)	-40 °C
Max. temperatur	100 °C
Flame-retardant	No
UV-resistant	No

Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

CE marking	Yes
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

SKINDICHT® KU-M

Article No.	Name	Outer thread	Inner thread	Colour description	Delivery Unit
52104469	SKINDICHT® KU-M 63X1.5/50X1.5 LGY	M 63	M 50	light gray	5
52104470	SKINDICHT® KU-M 20X1.5/12X1.5 LGY	M 20	M 12	light gray	100
52104472	SKINDICHT® KU-M 25X1.5/12X1.5 LGY	M 25	M 12	light gray	100
52104473	SKINDICHT® KU-M 25X1.5/16X1.5 LGY	M 25	M 16	light gray	100
52104474	SKINDICHT® KU-M 25X1.5/20X1.5 LGY	M 25	M 20	light gray	100
52104475	SKINDICHT® KU-M 32X1.5/12X1.5 LGY	M 32	M 12	light gray	50
52104476	SKINDICHT® KU-M 32X1.5/16X1.5 LGY	M 32	M 16	light gray	50
52104477	SKINDICHT® KU-M 32X1.5/20X1.5 LGY	M 32	M 20	light gray	50
52104478	SKINDICHT® KU-M 32X1.5/25X1.5 LGY	M 32	M 25	light gray	50
52104479	SKINDICHT® KU-M 40X1.5/16X1.5 LGY	M 40	M 16	light gray	50
52104480	SKINDICHT® KU-M 40X1.5/20X1.5 LGY	M 40	M 20	light gray	50
52104481	SKINDICHT® KU-M 40X1.5/25X1.5 LGY	M 40	M 25	light gray	25
52104482	SKINDICHT® KU-M 40X1.5/32X1.5 LGY	M 40	M 32	light gray	25
52104483	SKINDICHT® KU-M 50X1.5/20X1.5 LGY	M 50	M 20	light gray	5
52104484	SKINDICHT® KU-M 50X1.5/25X1.5 LGY	M 50	M 25	light gray	5
52104485	SKINDICHT® KU-M 50X1.5/32X1.5 LGY	M 50	M 32	light gray	5
52104486	SKINDICHT® KU-M 50X1.5/40X1.5 LGY	M 50	M 40	light gray	5
52104487	SKINDICHT® KU-M 63X1.5/25X1.5 LGY	M 63	M 25	light gray	5
52104488	SKINDICHT® KU-M 63X1.5/32X1.5 LGY	M 63	M 32	light gray	5
52104489	SKINDICHT® KU-M 63X1.5/40X1.5 LGY	M 63	M 40	light gray	5
52104504	SKINDICHT® KU-M20X1.5/16X1.5 LGY	M 20	M 16	light gray	100
52104505	SKINDICHT® KU-M 16X1,5/12X1,5 LGY	M 16	M 12	light gray	100
52104520	SKINDICHT® KU-M 20/12 BK	M 20	M 12	black	100
52104521	SKINDICHT® KU-M 20/16 BK	M 20	M 16	black	100
52104523	SKINDICHT® KU-M 25/16 BK	M 25	M 16	black	100
52104524	SKINDICHT® KU-M 25/20 BK	M 25	M 20	black	100
52104526	SKINDICHT® KU-M 32/16 BK	M 32	M 16	black	50
52104527	SKINDICHT® KU-M 32/20 BK	M 32	M 20	black	50
52104528	SKINDICHT® KU-M 32/25 BK	M 32	M 25	black	50
52104530	SKINDICHT® KU-M 40/20 BK	M 40	M 20	black	50

Article No.	Name	Outer thread	Inner thread	Colour description	Delivery Unit
52104531	SKINDICHT® KU-M 40/25 BK	M 40	M 25	black	25
52104532	SKINDICHT® KU-M 40/32 BK	M 40	M 32	black	25
52104536	SKINDICHT® KU-M 50/40 BK	M 50	M 40	black	5
52104540	SKINDICHT® KU-M 63/50 BK	M 63	M 50	black	5
52104541	SKINDICHT® KU-M 16/12 BK	M 16	M 12	black	100

V1.1