

SKINDICHT® MR-M ATEX 32X1.5/25X1.5
Article No.: 52104573

Reducer; Inner thread: M 25; Outer thread: M 32; Brass Nickel-plated; For use in ex-atmospheres



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	SKINDICHT®
Product type	Reducer
Scope of delivery	including O-ring
Delivery with lock nut	No

Including o-ring	Yes
Type of packaging	Bag
Delivery Unit	25
Mounting method	in threaded borehole
Industry segment	Rolling Stock

Electrical parameters

Product design

Cable gland design	Straight
Inner thread	M 25
Outer thread	M 32
Total length	0.65 in
Overall width	1.465 in
Thread type	Metric
Thread size	M 32
Pitch of thread	1,5
Thread length	0.315 in
Thread standard	DIN EN 60423
Wrench width	1.339 in
Seal type	O-ring
Material o-ring	Acrylonitrile butadiene rubber
O-ring material, short form	NBR
Body material	Brass
Body material, short form	CuZn
Surface protection	Nickel-plated
Colour description	metal

Product features

IP protection rating	IP 66 IP 68
Suitable for EX-applications	Yes

Temperature (min.)	-30 °C
Max. temperatur	90 °C
Flame-retardant	Yes
UV-resistant	Yes
Halogenfree	No
Oil resistant	Yes

Certifications and standards

CE marking	Yes
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
ATEX certification	IECEX IBE 13.0028X : Ex II 2G Ex eb IIC Ex II 1D Ex ta IIIC
CCCEX-certified	Yes
GGVS certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

SKINDICHT® MR-M ATEX

Article No.	Name	Outer thread	Inner thread	Delivery Unit
52104570	SKINDICHT® MR-M ATEX16X1.5/12X1.5	M 16	M 12	50
52104571	SKINDICHT® MR-M ATEX 20X1.5/16X1.5	M 20	M 16	50
52104572	SKINDICHT® MR-M ATEX 25X1.5/20X1.5	M 25	M 20	25
52104573	SKINDICHT® MR-M ATEX 32X1.5/25X1.5	M 32	M 25	25
52104574	SKINDICHT® MR-M ATEX 40X1.5/32X1.5	M 40	M 32	10
52104575	SKINDICHT® MR-M ATEX 50X1.5/40X1.5	M 50	M 40	5
52104576	SKINDICHT® MR-M ATEX 63X1.5/50X1.5	M 63	M 50	5

V1.1