

SKINDICHT® SRE-M 32X1.5/29/23/19

Article No.: 52105700

Cable gland; M 32; Clamping range (min./max.): 0.827 - 0.906 in; Wrench width 1: 1.575; Brass Nickel-plated; UV-resistant; IP 65; EMC shielding



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	SKINDICHT®
Product type	Cable gland
Scope of delivery	including O-ring
Delivery with lock nut	No

Including o-ring	Yes
Type of packaging	Bag
Delivery Unit	10
Mounting method	in threaded borehole

Electrical parameters

Product design

For armored cables	No
Glass-fibre reinforced	No
Number of cable entries	1 pc.
With bending protection	Yes
Cable gland design	Straight
Total length	3.543 in
Overall width	1.85 in
Clear width	0.748 in
Thread type	Metric
Thread size	M 32
Pitch of thread	1,5
Thread length	0.315 in
Thread standard	DIN EN 60423
Spanner size 1	1.575 in
Wrench size 2	1.614 in
Hexagon corner dimensions	1.815 in
Clamping range min.	0.827 in
Clamping range max.	0.906 in
EMC shielding	Yes
Seal type	Sealing cone
Thread-side sealing element	O-ring
Cable-side sealing element	Anti-kink sleeve
Material o-ring	Acrylonitrile butadiene rubber
O-ring material, short form	NBR
Material sealing	Chloroprene rubber

Body material	Brass
Body material, short form	CuZn
Surface protection	Nickel-plated
Colour description	metal

Product features

IP protection rating	IP 65
Suitable for EX-applications	No
Temperature static min.	-20 °C
Max. static temperature	80 °C
Temperature (min.)	-20 °C
Max. temperatur	80 °C
Flame-retardant	No
UV-resistant	Yes
Halogenfree	No
Oil resistant	Yes
Impact proof	Yes
Strain relief	Yes

Certifications and standards

CE marking	Yes
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
For Ex zone gas	without
For Ex-zone dust	without
GGVS certified	No
DNV-certified	No
Ecolab certified	No
NSF certified	No

FDA certified	No
---------------	----

EHEDG certified	No
-----------------	----

SKINDICHT® SRE-M

Article No.	Name	Thread size	Thread length	Clamping range min.	Clamping range max.	Spanner size 1	Delivery Unit
52105600	SKINDICHT® SRE-M 20X1.5/13.5/9/6	M 20	0.236 in	0.295 in	0.354 in	0.866 in	25
52105610	SKINDICHT® SRE-M 20X1.5/13.5/11/7	M 20	0.236 in	0.354 in	0.433 in	0.866 in	25
52105620	SKINDICHT® SRE-M 20X1.5/16/13/9	M 20	0.236 in	0.433 in	0.512 in	0.945 in	25
52105630	SKINDICHT® SRE-M 20X1.5/16/13/10	M 20	0.236 in	0.433 in	0.512 in	0.945 in	25
52105640	SKINDICHT® SRE-M 20X1.5/16/15/11	M 20	0.236 in	0.531 in	0.591 in	0.945 in	25
52105650	SKINDICHT® SRE-M 25X1.5/21/15/12	M 25	0.276 in	0.531 in	0.591 in	1.181 in	25
52105660	SKINDICHT® SRE-M 25X1.5/21/17/14	M 25	0.276 in	0.591 in	0.669 in	1.181 in	25
52105670	SKINDICHT® SRE-M 25X1.5/21/19/15	M 25	0.276 in	0.669 in	0.748 in	1.181 in	25
52105680	SKINDICHT® SRE-M 25X1.5/21/20/16	M 25	0.276 in	0.709 in	0.787 in	1.181 in	25
52105700	SKINDICHT® SRE-M 32X1.5/29/23/19	M 32	0.315 in	0.827 in	0.906 in	1.575 in	10
52105710	SKINDICHT® SRE-M 40X1.5/36/26/22	M 40	0.315 in	0.925 in	1.024 in	1.969 in	5
52105720	SKINDICHT® SRE-M 40X1.5/36/30/24	M 40	0.315 in	1.063 in	1.181 in	1.969 in	5
52105730	SKINDICHT® SRE-M 40X1.5/36/33/28	M 40	0.315 in	1.181 in	1.299 in	1.969 in	5
52105740	SKINDICHT® SRE-M 40/36/35/30	M 40	0.315 in	1.26 in	1.378 in	1.969 in	5

V1.1