

SKINDICHT® KW-M 25X1.5

Article No.: 52106230

Angled cable gland; M 25; Polyamide Uncoated; Halogen-free; 90° angle; IP 55



CE



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	SKINDICHT®
Product type	Angled cable gland
Delivery with lock nut	No
Including o-ring	No

Type of packaging	Bag
Delivery Unit	25
Mounting method	in threaded borehole

Electrical parameters

Product design

For armored cables	No
Glass-fibre reinforced	Yes
Number of cable entries	1 pc.
With bending protection	No
Cable gland design	90° angle
Overall width	1.693 in
Overall height	1.909 in
Clear width	0.787 in
Thread type	Metric
Thread size	M 25
Pitch of thread	1,5
Thread length	0.63 in
Thread standard	DIN EN 60423
Spanner size 1	1.181 in
Wrench width	1.181 in
EMC shielding	No
Body material	Polyamide
Body material, short form	PA
Surface protection	Uncoated
Colour description	silver gray
RAL color	RAL 7001

Product features

IP protection rating	IP 55
Suitable for EX-applications	No

Temperature (min.)	-20 °C
Max. temperatur	80 °C
Flame-retardant	No
UV-resistant	Yes
Chemical resistant	Yes
Halogenfree	Yes
Oil resistant	Yes
Impact proof	No
Vibration protection	No
Strain relief	No

Certifications and standards

CE marking	Yes
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
For Ex zone gas	without
For Ex-zone dust	without
GGVS certified	No
DNV-certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

SKINDICHT® KW-M

Article No.	Name	Thread size	Wrench width	Delivery Unit
52106210	SKINDICHT® KW-M 16X1.5	M 16	0.748 in	25
52106220	SKINDICHT® KW-M 20X1.5	M 20	0.984 in	25
52106230	SKINDICHT® KW-M 25X1.5	M 25	1.181 in	25
52106240	SKINDICHT® KW-M 32X1.5	M 32	1.417 in	10

V1.1