

**SKINDICHT® RWV-M 16X1.5 WO. E+D****Article No.:** 52107811

Angled cable gland; M 16; Zinc alloy Nickel-plated; Halogen-free; 90° angle;

**CE****Details****Application**

- Machine and equipment manufacturing
- Plant engineering

**Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

### Remarks

### Technical Data

#### General information

Brand	SKINDICHT®
Product type	Angled cable gland
Scope of delivery	including O-ring
Delivery with lock nut	No
Including o-ring	Yes
Type of packaging	Bag
Delivery Unit	25
Mounting method	in threaded borehole
Industry segment	Lifts & Elevators Rolling Stock

#### Electrical parameters

#### Product design

For armored cables	No
Glass-fibre reinforced	No
Number of cable entries	1 pc.
With bending protection	No
Cable gland design	90° angle
Clear width	0.472 in
Thread type	Metric
Thread size	M 16
Pitch of thread	1,5
Thread length	0.256 in
Thread standard	DIN EN 60423
Spanner size 1	0.709 in
Wrench size 2	0.63 in

Hexagon corner dimensions	0.965 in
Wrench width	0.866 in
EMC shielding	No
Seal type	O-ring
Thread-side sealing element	O-ring
Material o-ring	Acrylonitrile butadiene rubber
O-ring material, short form	NBR
Body material	Zinc alloy
Surface protection	Nickel-plated
Colour description	metal

#### Product features

Suitable for EX-applications	No
Temperature (min.)	-20 °C
Max. temperatur	100 °C
Flame-retardant	Yes
UV-resistant	Yes
Halogenfree	Yes
Oil resistant	Yes
Impact proof	Yes
Vibration protection	No
Strain relief	No

#### Certifications and standards

CE marking	Yes
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
For Ex zone gas	without
For Ex-zone dust	without

---

GGVS certified	No
DNV-certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

---

---

**SKINDICHT® RWV-M without E+D**

Article No.	Name	Thread size	Thread length	Spanner size 1	Delivery Unit
52107801	SKINDICHT® RWV-M 12X1.5 WO. E+D	M 12	0.256 in	0.551 in	25
52107811	SKINDICHT® RWV-M 16X1.5 WO. E+D	M 16	0.256 in	0.709 in	25
52107821	SKINDICHT® RWV-M 20X1.5 WO. E+D	M 20	0.295 in	0.866 in	25
52107831	SKINDICHT® RWV-M 25X1.5 WO. E+D	M 25	0.335 in	1.063 in	10
52107841	SKINDICHT® RWV-M 32X1.5 WO. E+D	M 32	0.335 in	1.339 in	10

V1.1