

SKINTOP® GMP-GL PG 7 RAL 7035 LGY

Article No.: 53019001

Lock nut; PG 7; Wrench width: 0.748in; light gray; Polyamide; Halogenfree;



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	SKINTOP®
Product type	Lock nut
Type of packaging	Bag

Delivery Unit	100
Industry segment	Agricultural & Farm Machinery Lifts & Elevators

Electrical parameters

Product design

Glass-fibre reinforced	Yes
Thickness	0.197 in
Thread type	PG
Thread size	PG 7
Pitch of thread	1,27
Hexagon corner dimensions	0.827 in
Wrench width	0.748 in
EMC shielding	No
Body material	Polyamide
Body material, short form	PA
Surface protection	Uncoated
Colour description	light gray
RAL color	RAL 7035

Product features

Suitable for EX-applications	No
Temperature dynamic min.	-20 °C
Max. dynamic temperature	100 °C
Temperature static min.	-40 °C
Max. static temperature	100 °C
Temperature (min.)	-40 °C
Max. temperatur	100 °C
Flame-retardant	Yes
Flame retardance according to	UL 94 V-2
UV-resistant	No

Chemical resistant	Yes
Acid-resistant	No
Halogenfree	Yes
Oil resistant	Yes
Impact proof	No

Certifications and standards

CE marking	Yes
UL recognized	Yes
UL listed	No
cUR recognized	Yes
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
Tested for fire protection for railway vehicles	No
Ecolab certified	No
NSF certified	No
FDA certified	No
EHEDG certified	No

SKINTOP® GMP-GL

Article No.	Name	Thread size	Wrench width	Colour description	Delivery Unit
53019000	SKINTOP® GMP-GL PG 7 RAL 7001 SGY	PG 7	0.748 in	silver gray	100
53019001	SKINTOP® GMP-GL PG 7 RAL 7035 LGY	PG 7	0.748 in	light gray	100
53019010	SKINTOP® GMP-GL PG 9 RAL 7001 SGY	PG 9	0.866 in	silver gray	100
53019011	SKINTOP® GMP-GL PG 9 RAL 7035 LGY	PG 9	0.866 in	light gray	100
53019020	SKINTOP® GMP-GL PG 11 RAL 7001 SGY	PG 11	0.945 in	silver gray	100
53019021	SKINTOP® GMP-GL PG 11 RAL 7035 LGY	PG 11	0.945 in	light gray	100
53019030	SKINTOP® GMP-GL PG 13.5 RAL 7001 SGY	PG 13,5	1.063 in	silver gray	100
53019031	SKINTOP® GMP-GL PG 13.5 RAL 7035 LGY	PG 13,5	1.063 in	light gray	100
53019040	SKINTOP® GMP-GL PG 16 RAL 7001 SGY	PG 16	1.181 in	silver gray	100
53019041	SKINTOP® GMP-GL PG 16 RAL 7035 LGY	PG 16	1.181 in	light gray	100
53019050	SKINTOP® GMP-GL PG 21 RAL 7001 SGY	PG 21	1.417 in	silver gray	50
53019051	SKINTOP® GMP-GL PG 21 RAL 7035 LGY	PG 21	1.417 in	light gray	50
53019060	SKINTOP® GMP-GL PG 29 RAL 7001 SGY	PG 29	1.811 in	silver gray	50
53019061	SKINTOP® GMP-GL PG 29 RAL 7035 LGY	PG 29	1.811 in	light gray	50
53019070	SKINTOP® GMP-GL PG 36 RAL 7001 SGY	PG 36	2.362 in	silver gray	25
53019071	SKINTOP® GMP-GL PG 36 RAL 7035 LGY	PG 36	2.362 in	light gray	25
53019080	SKINTOP® GMP-GL PG 42 RAL 7001 SGY	PG 42	2.559 in	silver gray	25
53019081	SKINTOP® GMP-GL PG 42 RAL 7035 LGY	PG 42	2.559 in	light gray	25
53019090	SKINTOP® GMP-GL PG 48 RAL 7001 SGY	PG 48	2.756 in	silver gray	25
53019091	SKINTOP® GMP-GL PG 48 RAL 7035 LGY	PG 48	2.756 in	light gray	25
53019200	SKINTOP® GMP-GL PG 7 RAL 9005 BK	PG 7	0.748 in	black	100
53019210	SKINTOP® GMP-GL PG 9 RAL 9005 BK	PG 9	0.866 in	black	100
53019220	SKINTOP® GMP-GL PG 11 RAL 9005 BK	PG 11	0.945 in	black	100
53019230	SKINTOP® GMP-GL PG 13.5 RAL 9005 BK	PG 13,5	1.063 in	black	100
53019240	SKINTOP® GMP-GL PG 16 RAL 9005 BK	PG 16	1.181 in	black	100
53019250	SKINTOP® GMP-GL PG 21 RAL 9005 BK	PG 21	1.417 in	black	50
53019260	SKINTOP® GMP-GL PG 29 RAL 9005 BK	PG 29	1.811 in	black	50
53019270	SKINTOP® GMP-GL PG 36 RAL 9005 BK	PG 36	2.362 in	black	25
53019280	SKINTOP® GMP-GL PG 42 RAL 9005 BK	PG 42	2.559 in	black	25
53019290	SKINTOP® GMP-GL PG 48 RAL 9005 BK	PG 48	2.756 in	black	25

V1.1