

SKINTOP® GMP-GL NPT 1IN RAL 7001 SGY o.B.

Article No.: 53019331

Lock nut; NPT 1"; Wrench width: 1.614in; silver gray; Polyamide; Halogen-free;



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

 Technical Data

General information

Brand	SKINTOP®
Product type	Lock nut
Type of packaging	Bag
Delivery Unit	100

Electrical parameters
Product design

Glass-fibre reinforced	Yes
Thickness	0.295 in
Thread type	NPT
Thread size	NPT 1"
Pitch of thread	2,21
Hexagon corner dimensions	1.78 in
Wrench width	1.614 in
EMC shielding	No
Body material	Polyamide
Body material, short form	PA
Surface protection	Uncoated
Colour description	silver gray
RAL color	RAL 7001

Product features

Suitable for EX-applications	No
Temperature dynamic min.	-20 °C
Max. dynamic temperature	100 °C
Temperature static min.	-40 °C
Max. static temperature	100 °C
Temperature (min.)	-40 °C
Max. temperatur	100 °C

Flame-retardant	Yes
Flame retardance according to	UL 94 HB
UV-resistant	No
Chemical resistant	Yes
Acid-resistant	No
Halogenfree	Yes
Oil resistant	Yes
Impact proof	No

Certifications and standards

CE marking	Yes
UL recognized	No
UL listed	Yes
cUR recognized	No
cUL listed	Yes
CSA certified	No
VDE certified	No
GGVS certified	No
Tested for fire protection for railway vehicles	No
Ecolab certified	No
NSF certified	No
FDA certified	No
EHEDG certified	No

SKINTOP® GMP-GL NPT

Article No.	Name	Thread size	Wrench width	Colour description	Delivery Unit
53019300	SKINTOP® GMP-GL NPT 3/8IN RAL 7035 LGY o.	NPT 3/8"	0.866 in	light gray	100
53019301	SKINTOP® GMP-GL NPT 3/8IN RAL 7001 SGY o.	NPT 3/8"	0.866 in	silver gray	100
53019305	SKINTOP® GMP-GL NPT 3/8IN RAL 9005 BK o.B	NPT 3/8"	0.866 in	black	100
53019310	SKINTOP® GMP-GL NPT 1/2IN RAL 7035 LGY o.	NPT 1/2"	1.063 in	light gray	100
53019311	SKINTOP® GMP-GL NPT 1/2IN RAL 7001 SGY o.	NPT 1/2"	1.063 in	silver gray	100
53019315	SKINTOP® GMP-GL NPT 1/2IN RAL 9005 BK o.B	NPT 1/2"	1.063 in	black	100
53019320	SKINTOP® GMP-GL NPT 3/4IN RAL 7035 LGY o.	NPT 3/4"	1.417 in	light gray	100
53019321	SKINTOP® GMP-GL NPT 3/4IN RAL 7001 SGY o.	NPT 3/4"	1.417 in	silver gray	100
53019325	SKINTOP® GMP-GL NPT 3/4IN RAL 9005 BK o.B	NPT 3/4"	1.417 in	black	100
53019330	SKINTOP® GMP-GL NPT 1IN RAL 7035 LGY o.B.	NPT 1"	1.614 in	light gray	100
53019331	SKINTOP® GMP-GL NPT 1IN RAL 7001 SGY o.B.	NPT 1"	1.614 in	silver gray	100
53019335	SKINTOP® GMP-GL NPT 1IN RAL 9005 BK o.B.	NPT 1"	1.614 in	black	100

V1.1