

SKINTOP® DIX-DV 5.5X11**Article No.:** 53100055

Sealing insert; natural

**Details****Benefits**

- Prevents liquid and dirt from penetrating unused holes of SKINTOP® DIX-M multiple sealing inserts.
- This enables protection class IP 68 for the SKINTOP® DIX-M multiple sealing insert to be achieved.
- Available in different variants according to the selected multi-sealing insert.

Application

- Can be used in combination with SKINTOP® DIX-M multiple sealing inserts in SKINTOP® cable glands.

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Delivery will be made in the largest possible packing unit (bulk goods), minimum order quantity is one PU.

Technical Data

General information

Brand	SKINTOP®
Product type	Sealing insert
Type of packaging	Bag
Delivery Unit	100
Industry segment	Solar

Electrical parameters

Product design

Slotted	No
Outer diameter	0.217 in
Overall height	0.433 in
EMC shielding	No
Material	Polyamide
Colour description	natural

Product features

Suitable for EX-applications	No
Temperature (min.)	-40 °C
Max. temperatur	100 °C
Flame-retardant	No
UV-resistant	No
Chemical resistant	Yes
Acid-resistant	No
Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

CE marking	No
------------	----

Ecolab certified	No
------------------	----

SKINTOP® DIX-DV

Article No.	Name	Outer diameter	Delivery Unit
53100003	SKINTOP® DIX-DV 3X9	0.118 in	100
53100004	SKINTOP® DIX-DV 4X9	0.157 in	100
53100005	SKINTOP® DIX-DV 5X11	0.197 in	100
53100006	SKINTOP® DIX-DV 6X14	0.236 in	100
53100007	SKINTOP® DIX-DV 7X14	0.276 in	100
53100008	SKINTOP® DIX-DV 8X14	0.315 in	100
53100009	SKINTOP® DIX-DV 9X14	0.354 in	100
53100055	SKINTOP® DIX-DV 5.5X11	0.217 in	100

V1.1