

SKINTOP® DIX-M 25154 SLOTTED
Article No.: 53440980

Sealing insert; M 25; Number of cable entries: 1pc.; Bore diameter: 0.213in; black


CE

Details
Benefits

- Special design with round pre-drilled bore and longitudinal cut for easy insertion of one or more pre-assembled data cables.
- Protection class IP 68 can be achieved if the bores are optimally occupied.
- High functional reliability thanks to optimum strain relief.

Application

- For use with metric SKINTOP®/SKINTOP® CLICK cable glands.
- To be used instead of the standard sealing insert in the SKINTOP® cable gland.
- UV and oil-resistant material.

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	SKINTOP®
Product type	Sealing insert
Type of packaging	Bag
Delivery Unit	50

Electrical parameters

Product design

Number of cable entries	1 pc.
Slotted	Yes
Overall height	0.374 in
Bore diameter	0.213 in
Thread size	M 25
Clamping range max.	0.213 in
EMC shielding	No
Material	Acrylonitrile butadiene rubber
Colour description	black

Product features

IP protection rating	IP 66 IP 68 - 5 g/cm ² (30 min)
----------------------	---

Suitable for EX-applications	No
Temperature (min.)	-40 °C
Max. temperatur	100 °C
Flame-retardant	No
UV-resistant	No
Chemical resistant	Yes
Acid-resistant	No
Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

CE marking	Yes
Ecolab certified	No

SKINTOP® DIX-M AUTOMATION slotted

Article No.	Name	Thread size	Number of cable entries	Delivery Unit	Clamping range min.	Clamping range max.
53310444	SKINTOP® DIX-M 40310 SLOTTED	M 40	3 pc.	25	0.276 in	0.394 in
53440970	SKINTOP® DIX-M 32165 SLOTTED	M 32	1 pc.	50	0.177 in	0.256 in
53440980	SKINTOP® DIX-M 25154 SLOTTED	M 25	1 pc.	50		0.213 in
53440982	SKINTOP® DIX-M 25170 SLOTTED	M 25	1 pc.	50	0.118 in	0.276 in
53440983	SKINTOP® DIX-M 25190 SLOTTED	M 25	1 pc.	50	0.157 in	0.354 in
53611005	SKINTOP® DIX-M 32111 SLOTTED	M 32	1 pc.	50	0.236 in	0.433 in
53611006	SKINTOP® DIX-M 32185 SLOTTED	M 32	1 pc.	50	0.197 in	0.335 in
53611007	SKINTOP® DIX-M 32380 SLOTTED	M 32	3 pc.	50	0.236 in	0.315 in
53611008	SKINTOP® DIX-M 40490 SLOTTED	M 40	4 pc.	25	0.256 in	0.354 in

V1.1