

**SKINTOP® DIX-M 25 ASI BUS DUO****Article No.:** 53611004

Multiple sealing insert; M 25; Number of cable entries: 2pc.; black

**CE****Details****Benefits**

- Protection class IP 68 can be achieved if the bores are optimally occupied.
- High functional reliability thanks to optimum strain relief.

**Application**

- For use with metric SKINTOP®/SKINTOP® CLICK cable glands.
- To be used instead of the standard sealing insert in the SKINTOP® cable gland.
- UV and oil-resistant material.

**Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

### Remarks

### Technical Data

#### General information

Brand	SKINTOP®
Product type	Multiple sealing insert
Type of packaging	Bag
Delivery Unit	50

#### Electrical parameters

#### Product design

Number of cable entries	2 pc.
Slotted	No
Overall height	0.331 in
Thread size	M 25
EMC shielding	No
Material	Acrylonitrile butadiene rubber
Colour description	black

#### Product features

IP protection rating	IP 68 - 5 g/cm <sup>2</sup> (30 min) IP 54
Suitable for EX-applications	No
Temperature (min.)	-40 °C

---

Max. temperatur	100 °C
Flame-retardant	No
UV-resistant	No
Chemical resistant	Yes
Acid-resistant	No
Halogenfree	Yes
Oil resistant	Yes

---

**Certifications and standards**

CE marking	Yes
Ecolab certified	No

---

---

**SKINTOP® DIX-M AUTOMATION AS-I**

Article No.	Name	Thread size	Number of cable entries	Delivery Unit
53611001	SKINTOP® DIX ASI-M 20	M 20	1 pc.	50
53611004	SKINTOP® DIX-M 25 ASI BUS DUO	M 25	2 pc.	50

V1.1