

SKINTOP® SDVR-M 16 ATEX**Article No.:** 54113013

Sealing insert; M 16; black

**Details****Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks**Technical Data****General information**

Brand	SKINTOP®
Product type	Sealing insert
Type of packaging	Bag
Delivery Unit	50

Electrical parameters

Product design

Slotted	No
Overall height	0.551 in
Thread size	M 16
EMC shielding	No
Material	Chloroprene rubber
Material shortname	CR
Colour description	black

Product features

IP protection rating	IP 66 IP 68 - 10 g/cm ² (30 min)
Suitable for EX-applications	Yes
Short term temperature max.	90 °C
Temperature (min.)	-30 °C
Max. temperatur	70 °C
Flame-retardant	No
UV-resistant	Yes
Chemical resistant	Yes
Acid-resistant	No
Halogenfree	No
Oil resistant	Yes

Certifications and standards

CE marking	Yes
ATEX certification	IECEX IBE 13.0026X : Ex II 2G Ex eb IIC Ex II 1D Ex ta IIIC
CCCEX-certified	Yes
Ecolab certified	No

SKINTOP® SDV-M ATEX

Article No.	Name	Thread size	Delivery Unit
54113002	SKINTOP® SDV-M 12 ATEX	M 12	50
54113012	SKINTOP® SDV-M 16 ATEX	M 16	50
54113013	SKINTOP® SDVR-M 16 ATEX	M 16	50
54113022	SKINTOP® SDV-M 20 ATEX	M 20	50
54113023	SKINTOP® SDVR-M 20 ATEX	M 20	50
54113032	SKINTOP® SDV-M 25 ATEX	M 25	50
54113033	SKINTOP® SDVR-M 25 ATEX	M 25	25
54113042	SKINTOP® SDV-M 32 ATEX	M 32	25
54113052	SKINTOP® SDV-M 40 ATEX	M 40	25
54113062	SKINTOP® SDV-M 50 ATEX	M 50	10
54113072	SKINTOP® SDV-M 63 ATEX	M 63	5

V1.1