

**SILVYN® KLICK 90° M25X 1.5/1 BK**

**Article No.:** 55501175

Angled conduit connector; M 25; Suitable for protective cable conduit size: 21;  
Polyamide; Halogen-free; UV-resistant; IP 68, IP 69;



**Details**

**Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

**Remarks**

**Technical Data**

**General information**

Brand	SILVYN®
Product type	Angled conduit connector
Delivery with lock nut	No

Including o-ring	No
Delivery Unit	50

### Electrical parameters

#### Product design

suitable for protective conduit size	21
With bending protection	No
Bending protection fixed installation	No
Flexibly installed bending protection	No
Conduit gland design	90° angle
Overall width	1.929 in
Overall height	1.969 in
Clear width	0.709 in
Thread type	Metric
Thread size	M 25
Pitch of thread	1,5
Thread standard	DIN EN 60423
Material o-ring	Acrylonitrile butadiene rubber
O-ring material, short form	NBR
Material sealing	Thermoplastic elastomers
Body material	Polyamide
Body material, short form	PA
Colour description	black
RAL color	RAL 9005

#### Product features

IP protection rating	IP 68 IP 69
Suitable for EX-applications	No
Flame-retardant	Yes
Flame retardance according to	UL 94 HB

---

UV-resistant	Yes
Chemical resistant	Yes
Halogenfree	Yes
Oil resistant	Yes

---

**Certifications and standards**

CE marking	Yes
UL recognized	Yes
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	Yes
GGVS certified	No
DNV-certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

---

**SILVYN® KLICK 90° M**

Article No.	Name	Thread size	Colour description	suitable for protective conduit size	Delivery Unit
55501110	SILVYN® KLICK 90° M10X1.0 GY	M 10	gray	10	50
55501115	SILVYN® KLICK 90° M10X1.0 BK	M 10	black	10	50
55501120	SILVYN® KLICK 90° M12X1.5 GY	M 12	gray	13	50
55501125	SILVYN® KLICK 90° M12X1.5 BK	M 12	black	13	50
55501130	SILVYN® KLICK 90° M16X1.5/1 GY	M 16	gray	13	50
55501135	SILVYN® KLICK 90° M16X1.5/1 BK	M 16	black	13	50
55501140	SILVYN® KLICK 90° M16X1.5/2 GY	M 16	gray	16	50
55501145	SILVYN® KLICK 90° M16/2 15.8 BK	M 16	black	16	50
55501150	SILVYN® KLICK 90° M20X1.5/1 GY	M 20	gray	16	50
55501155	SILVYN® KLICK 90° M20X 1.5/1 BK	M 20	black	16	50
55501160	SILVYN® KLICK 90° M20X1.5/2 GY	M 20	gray	21	50
55501165	SILVYN® KLICK 90° M20X 1.5/2 BK	M 20	black	21	50
55501170	SILVYN® KLICK 90° M25X1.5/1 GY	M 25	gray	21	50
55501175	SILVYN® KLICK 90° M25X 1.5/1 BK	M 25	black	21	50
55501180	SILVYN® KLICK 90° M25X1.5/2 GY	M 25	gray	28	25
55501185	SILVYN® KLICK 90° M25X1.5/2 BK	M 25	black	28	25
55501195	SILVYN® KLICK 90° M32X1.5/1 BK	M 32	black	28	25
55501200	SILVYN® KLICK 90° M32X1.5/2 GY	M 32	gray	34	10
55501205	SILVYN® KLICK 90° M32X1.5/2 BK	M 32	black	34	10
55501210	SILVYN® KLICK 90° M40X1.5/1 GY	M 40	gray	34	10
55501215	SILVYN® KLICK 90° M40X 1.5/1 BK	M 40	black	34	10
55501220	SILVYN® KLICK 90° M40X1.5/2 GY	M 40	gray	42	10
55501225	SILVYN® KLICK 90° M40X1.5/2 BK	M 40	black	42	10
55501240	SILVYN® KLICK 90° M50X1.5/2 GY	M 50	gray	54	5
55501245	SILVYN® KLICK 90° M50X1.5/2 BK	M 50	black	54	5
55501250	SILVYN® KLICK 90° M63X1.5 GY	M 63	gray	54	5
55501255	SILVYN® KLICK 90° M63X 1.5 BK	M 63	black	54	5

V1.1