

SILVYN® SSVZ-M 20X1.5/2

Article No.: 55501880

Conduit connector; M 20; Nominal size: 20; IP 68, IP 54;



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	SILVYN®
Product type	Conduit connector
Scope of delivery	including O-ring
Delivery with lock nut	No

Including o-ring	Yes
Type of packaging	Bag
Delivery Unit	50
Mounting method	in threaded borehole

Electrical parameters

Product design

With bending protection	No
Bending protection fixed installation	No
Flexibly installed bending protection	No
Slotted	No
Conduit gland design	Straight
Resistance against hot swarf	No
Divisible conduit gland	No
Rotatable thread	No
Outer diameter	0.866 in
Total length	1.559 in
Clear width	0.472 in
Nominal size	20 "
Thread size	M 20
Pitch of thread	1,5
Thread length	0.236 in
Thread standard	DIN EN 60423
Spanner size 1	0.866 in
Wrench size 2	0.866 in
Hexagon corner dimensions	0.945 in
EMC shielding	No
For conduit outer diameter	0.787 in
Seal type	Incized sealing ring
Material o-ring	Acrylonitrile butadiene rubber
O-ring material, short form	NBR
Incized sealing ring material	Chloroprene rubber

Incized sealing ring material, short form	CR
Gland body material	Brass
Material fitting body shortname	CuZn
Surface protection	Nickel-plated

Product features

IP protection rating	IP 68 IP 54
Suitable for EX-applications	No
Flame-retardant	No
UV-resistant	No
Chemical resistant	No
Acid-resistant	No
Halogenfree	No
Oil resistant	Yes
Impact proof	No
Strain relief	Yes

Certifications and standards

CE marking	Yes
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
DNV-certified	No
Tested for fire protection for railway vehicles	No
Ecolab certified	No
NSF certified	No

FDA certified	No
EHEDG certified	No

SILVYN® SSVZ-M

Article No.	Name	Thread size	Delivery Unit
55501860	SILVYN® SSVZ-M 16X1.5/2	M 16	50
55501870	SILVYN® SSVZ-M 20X1.5/1	M 20	50
55501880	SILVYN® SSVZ-M 20X1.5/2	M 20	50
55501910	SILVYN® SSVZ-M 25X1.5	M 25	25

V1.1