

SILVYN® US PG 11 EDU

Article No.: 55502682

Conduit connector; PG 11; Suitable for protective cable conduit size: 17; Halogen-free; UV-resistant; IP 40, IP 65;



CE



Details

Application

- Plant engineering

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	SILVYN®
Product type	Conduit connector
Scope of delivery	including O-ring
Including o-ring	Yes
Delivery Unit	50

Electrical parameters

Product design

suitable for protective conduit size	17
With bending protection	No
Bending protection fixed installation	No
Flexibly installed bending protection	No
Conduit gland design	Straight
Total length	1.181 in
Clear width	0.453 in
Thread type	PG
Thread size	PG 11
Pitch of thread	1,41
Thread length	0.276 in
Spanner size 1	0.906 in
Wrench size 2	0.984 in
EMC shielding	No
Material o-ring	Acrylonitrile butadiene rubber
O-ring material, short form	NBR
Screw-in sleeve material	Brass
Gland body material	Brass

Material fitting body shortname	CuZn
Surface protection	Nickel-plated

Product features

IP protection rating	IP 40 IP 65
Suitable for EX-applications	No
Flame-retardant	Yes
UV-resistant	Yes
Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

CE marking	Yes
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
DNV-certified	No
Ecolab certified	No
NSF certified	No
FDA certified	No
EHEDG certified	No

SILVYN® US

Article No.	Name	Thread size	suitable for protective conduit size	Delivery Unit
55502661	SILVYN® US PG 7 AS	PG 7	10	50
55502662	SILVYN® US PG 9 AS	PG 9	14	50
55502663	SILVYN® US PG 11 AS	PG 11	17	50
55502664	SILVYN® US PG 13.5 AS	PG 13,5	19	50
55502665	SILVYN® US PG 16 AS	PG 16	21	50
55502666	SILVYN® US PG 21 AS	PG 21	27	25
55502667	SILVYN® US PG 29 AS	PG 29	36	25
55502668	SILVYN® US PG 36 AS	PG 36	45	20
55502671	SILVYN® US PG 7 AS-P	PG 7	10	50
55502672	SILVYN® US PG 9 AS-P	PG 9	14	50
55502673	SILVYN® US PG 11 AS-P	PG 11	17	50
55502674	SILVYN® US PG 13.5 AS-P	PG 13,5	19	50
55502675	SILVYN® US PG 16 AS-P	PG 16	21	50
55502676	SILVYN® US PG 21 AS-P	PG 21	27	25
55502677	SILVYN® US PG 29 AS-P	PG 29	36	25
55502678	SILVYN® US PG 36 AS-P	PG 36	45	20
55502679	SILVYN® US PG 48 AS-P	PG 48	56	10
55502680	SILVYN® US PG 7 EDU	PG 7	10	50
55502682	SILVYN® US PG 11 EDU	PG 11	17	50
55502683	SILVYN® US PG 13.5 EDU	PG 13,5	19	50
55502684	SILVYN® US PG 16 EDU	PG 16	21	50
55502685	SILVYN® US PG 21 EDU	PG 21	27	25

V1.1