

SILVYN® FPAG 90° M16X1.5 / 16 BK

Article No.: 55506505

Angled conduit connector; M 16; Nominal size: 16; Suitable for protective cable conduit size: 16; Halogen-free; UV-resistant; IP 66;



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	SILVYN®
Product type	Angled conduit connector
Delivery with lock nut	No
Including o-ring	No

Delivery Unit	10
Mounting method	in threaded borehole

Electrical parameters

Product design

suitable for protective conduit size	16
With bending protection	No
Bending protection fixed installation	No
Flexibly installed bending protection	No
Slotted	No
Conduit gland design	90° angle
Resistance against hot swarf	No
Divisible conduit gland	No
Rotatable thread	No
Overall width	1.142 in
Overall height	1.496 in
Clear width	0.413 in
Nominal size	16 "
Thread type	Metric
Thread size	M 16
Pitch of thread	1,5
Thread length	0.433 in
Thread standard	DIN EN 60423
Lockable (two-part)	No
EMC shielding	No
For conduit outer diameter	0.63 in
Gland body material	Polyamide
Material fitting body shortname	PA

Product features

IP protection rating	IP 66
----------------------	-------

Suitable for EX-applications	No
Flame-retardant	Yes
Flame retardance according to	UL 94 V-2
UV-resistant	Yes
Halogenfree	Yes
Oil resistant	Yes
Strain relief	No

Certifications and standards

CE marking	Yes
UL recognized	Yes
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
DNV-certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

SILVYN® FPAG 90° M

Article No.	Name	Thread size	Colour description	suitable for protective conduit size	Delivery Unit
55506495	SILVYN® FPAG 90° M16X1.5 / 13 BK	M 16			13 10
55506505	SILVYN® FPAG 90° M16X1.5 / 16 BK	M 16			16 10
55506515	SILVYN® FPAG 90° M20X1.5 / 16 BK	M 20			16 10
55506525	SILVYN® FPAG 90° M20X1.5 / 21 BK	M 20			21 10
55506535	SILVYN® FPAG 90° M25X1.5 / 28 BK	M 25			28 10
55506536	SILVYN® FPAG 90° M25X1.5 / 25 BK	M 25			25 10
55506545	SILVYN® FPAG 90° M32X1.5 / 34 BK	M 32			34 10
55507075	SILVYN® FPAG 90° M20X1.5 / 18 BK	M 20			18 10
55507085	SILVYN® FPAG 90° M40X1.5 / 42 BK	M 40			42 1
55507095	SILVYN® FPAG 90° M63X1.5 / 67 BK	M 63			67 1

V1.1