

SILVYN® FCL 25 BK

Article No.: 55507415

Mounting bracket; Nominal size: 25; For conduit outer diameter: 0.984in; Polyamide



CE



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

| | |
|------------------------|------------------|
| Brand | SILVYN® |
| Product type | Mounting bracket |
| Delivery with lock nut | No |
| Including o-ring | No |

| | |
|-------------------|-------|
| Type of packaging | Bag |
| Delivery Unit | 10 |
| Mounting method | screw |

Electrical parameters**Product design**

| | |
|------------------------------|-----------|
| Slotted | No |
| Resistance against hot swarf | No |
| Divisible conduit gland | No |
| Rotatable thread | No |
| Overall width | 1.614 in |
| Overall height | 1.772 in |
| Nominal size | 25 " |
| EMC shielding | No |
| For conduit outer diameter | 0.984 in |
| Body material | Polyamide |
| Body material, short form | PA |
| Colour description | black |

Product features

| | |
|------------------------------|-----|
| Suitable for EX-applications | No |
| Flame-retardant | Yes |
| UV-resistant | Yes |
| Halogenfree | Yes |
| Oil resistant | Yes |
| Strain relief | No |

Certifications and standards

| | |
|-----------------|-----|
| CE marking | Yes |
| EHEDG certified | No |

SILVYN® FCL

| Article No. | Name | Nominal size | Colour description | Delivery Unit |
|-------------|-------------------|--------------|--------------------|---------------|
| 55506905 | SILVYN® FCL 10 BK | 10 " | black | 10 |
| 55506910 | SILVYN® FCL 13 GY | 13 " | gray | 10 |
| 55506915 | SILVYN® FCL 13 BK | 13 " | black | 10 |
| 55506920 | SILVYN® FCL 16 GY | 16 " | gray | 10 |
| 55506925 | SILVYN® FCL 16 BK | 16 " | black | 10 |
| 55506930 | SILVYN® FCL 21 GY | 21 " | gray | 10 |
| 55506935 | SILVYN® FCL 21 BK | 21 " | black | 10 |
| 55506940 | SILVYN® FCL 28 GY | 28 " | gray | 10 |
| 55506945 | SILVYN® FCL 28 BK | 28 " | black | 10 |
| 55506950 | SILVYN® FCL 34 GY | 34 " | gray | 10 |
| 55506954 | SILVYN® FCL 32 BK | 32 " | black | 10 |
| 55506955 | SILVYN® FCL 34 BK | 34 " | black | 10 |
| 55506960 | SILVYN® FCL 42 GY | 42 " | gray | 5 |
| 55506965 | SILVYN® FCL 42 BK | 42 " | black | 5 |
| 55506970 | SILVYN® FCL 54 GY | 54 " | gray | 5 |
| 55506975 | SILVYN® FCL 54 BK | 54 " | black | 5 |
| 55506985 | SILVYN® FCL 18 BK | 18 " | black | 10 |
| 55507405 | SILVYN® FCL 20 BK | 20 " | black | 10 |
| 55507415 | SILVYN® FCL 25 BK | 25 " | black | 10 |

V1.1