

**SILVYN® BMC-M 32X1.5****Article No.:** 55510030

Collar; M 32; Brass Nickel-plated; Halogen-free; UV-resistant;

**Details****Benefits**

- Connector for extending protective cable conduits.
- Easy assembly by screwing into the conduit connector thread.
- Can be combined with all metric conduit connectors.

**Application**

- For connecting two metric conduit connectors in protective cable conduits.
- Withstands high chemical and mechanical loads.
- Suitable for outdoor use.

**Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

**Remarks**

---

## Technical Data

### General information

Brand	SILVYN®
Product type	neck
Delivery with lock nut	No
Including o-ring	No
Type of packaging	Bag
Delivery Unit	10

### Electrical parameters

#### Product design

With bending protection	No
Conduit gland design	Straight
Total length	1.28 in
Overall width	1.516 in
Thread size	M 32
Pitch of thread	1,5
Thread standard	DIN EN 60423
Wrench width	1.378 in
EMC shielding	No
Body material	Brass
Body material, short form	CuZn
Surface protection	Nickel-plated

#### Product features

Suitable for EX-applications	No
Flame-retardant	Yes
UV-resistant	Yes
Halogenfree	Yes
Oil resistant	Yes

**Certifications and standards**

CE marking	No
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
GGVS certified	No
Ecolab certified	No
NSF certified	No
EHEDG certified	No

---

**SILVYN® coupler**

Article No.	Name	Thread size	Delivery Unit
55510000	SILVYN® BMC-M 16X1.5	M 16	10
55510010	SILVYN® BMC-M 20X1.5	M 20	10
55510020	SILVYN® BMC-M 25X1.5	M 25	10
55510030	SILVYN® BMC-M 32X1.5	M 32	10

V1.1