

**SILVYN® HIPROSILTAPPE 25X0.5**

**Article No.:** 61713040

Adhesive tape; Silicone



**Details**

**Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

**Remarks**

**Technical Data**

**General information**

Brand	SILVYN®
Product type	Adhesive tape
Type of packaging	Box
Delivery Unit	11
Mounting method	adhere
Industry segment	Rolling Stock

**Electrical parameters****Product design**

Slotted	No
Resistance against hot swarf	Yes
Overall width	0.984 in
Body material	Silicone
Colour description	red

**Product features**

Suitable for EX-applications	No
Flame-retardant	Yes
UV-resistant	Yes
Halogenfree	Yes
Oil resistant	Yes
Strain relief	No

**Certifications and standards**

CE marking	No
EHEDG certified	No

---

**SILVYN® HIPROSILTAPE**

Article No.	Name	Overall width	Delivery Unit
61713040	SILVYN® HIPROSILTAPE 25X0.5	0.984 in	11

V1.1