

SCREW / ADHESIVE SOCKET 28X28 NA**Article No.:** 61718614

Cable tie mount; for cable tie width: 0.209in; natural; Polyamide; Halogen-free;

**Details****Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

Remarks

Smooth, grease-free Walls required

Minimum adhesive application time: 10 sec, Recommended curing time: 24 h

Self-extinguishing according to UL 94 V2 (without adhesive tape)

Trade product, not a LAPP product.

 Technical Data

General information

Product type	Cable tie mount
Delivery Unit	100
pieces per PU	100 pc.

Electrical parameters
Product design

Total length	1.102 in
Overall width	1.102 in
Bore diameter	0.209 in
Material	Polyamide
Colour description	natural
for cable tie width	0.209 in

Product features

Installation temperature min.	10 °C
Flame-retardant	Yes
Flame retardance according to	UL 94 V-2
UV-resistant	No
Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No

DNV-certified	No
Ecolab certified	No

Tie socket self-adhesive

Article No.	Name	for cable tie width	Total length	Overall width	pieces per PU
61718611	SCREW / ADHESIVE SOCKET 19X19 BK	0.142 in	0.748 in	0.748 in	100 pc.
61718612	SCREW / ADHESIVE SOCKET 19X19 NA	0.142 in	0.748 in	0.748 in	100 pc.
61718613	SCREW / ADHESIVE SOCKET 28X28 BK	0.209 in	1.102 in	1.102 in	100 pc.
61718614	SCREW / ADHESIVE SOCKET 28X28 NA	0.209 in	1.102 in	1.102 in	100 pc.

V1.1