

CRIMPING PLIERS DSA 0725**Article No.:** 61722060Crimping tool; For cross-section (min./max.): 0.75mm² - 2.5mm²; Crimping profile: Oval**Details****Notes**

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

Remarks

Trade product, not a LAPP product.

Technical Data**General information**

Product type	Crimping tool
Delivery Unit	1

Electrical parameters

Product design

For pressing	Insulated panel connector Insulated cable lug
Total length	7.559 in
For cross-section (min.)	0.75 mm ²
For cross-section (max.)	2.5 mm ²
Colour description	orange/black
Crimping profile	Oval

Product features**Certifications and standards**

CE marking	No
VDE certified	No
TÜV certified	No

DSA 0110 + DSA 0725 Crimping pliers

Article No.	Name	For cross-section (min.)	For cross-section (max.)	Crimping profile
61722050	CRIMPING PLIERS DAS 0110	0.14 mm ²	1 mm ²	Oval
61722060	CRIMPING PLIERS DSA 0725	0.75 mm ²	2.5 mm ²	Oval

V1.1