

TIE MOUNTING SOCKET TC 142

Article No.: 61724910

Cable tie mount; for cable tie width: 0.299in; white; Polyamide; Halogen-free;



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

Remarks

Trade product, not a LAPP product.

Technical Data

General information

Product type	Cable tie mount
Scope of delivery	without screws

Delivery Unit	500
pieces per PU	500 pc.

Electrical parameters

Product design

Total length	0.921 in
Overall width	0.559 in
Overall height	0.433 in
Bore diameter	0.205 in
Material	Polyamide
Colour description	white
for cable tie width	0.299 in

Product features

Flame-retardant	Yes
Flame retardance according to	UL 94 V-2
UV-resistant	No
Halogenfree	Yes
Oil resistant	Yes

Certifications and standards

UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
DNV-certified	No
Ecolab certified	No

Mounting socket with saddle

Article No.	Name	for cable tie width	Total length	Overall width	pieces per PU
61724510	TIE MOUNTING SOCKET TC 141	0.189 in	0.669 in	0.437 in	500 pc.
61724910	TIE MOUNTING SOCKET TC 142	0.299 in	0.921 in	0.559 in	500 pc.
61724920	TIE MOUNTING SOCKET TC 140	0.11 in	0.559 in	0.343 in	500 pc.

V1.1