

ALLROUNDER STRIP STRIPPING TOOL**Article No.:** 61735835

Dismantling tool; Cable diameter: 0.157in - 0.591in; Conductor cross-section 1.5mm² - 50mm²;

**Details****Notes**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Trade product, not a LAPP product.

Remarks

Stripping and stripping of round and flat cables with two parallel blades (4-15 mm (0.58 in) Ø (round cable), max. 15mm width (flat cable))

Extra blade for longitudinal cutting

2 stripping blades for single conductors

Locator box for limiting the blade spacing

Trade product, not a LAPP product.

Technical Data

General information

Product type	Dismantling tool
Delivery Unit	1
suitable for	Cables Solid conductor Flexible conductors Round cables Shielded cables Single conductors Flat cables

Electrical parameters

Product design

Total length	5.118 in
Overall width	1.496 in
Overall height	0.945 in
For min. cable outer diameter	0.157 in
For max. cable outer diameter	0.591 in
For cross-section (min.)	1.5 mm ²
For cross-section (max.)	50 mm ²
Material	Polyamide
material blade	Steel
Blade shape	Straight

Product features**Certifications and standards**

CE marking	No
VDE certified	No
TÜV certified	Yes
GS certified	Yes

ALLROUNDER STRIP dismantling tool

Article No.	Name	For min. cable outer diameter	For max. cable outer diameter	For cross-section (min.)	For cross-section (max.)	Product type
61735835	ALLROUNDER STRIP STRIPPING TOOL	0.157 in	0.591 in	1.5 mm ²	50 mm ²	Dismantling tool
61735836	ALLROUNDER LOCATOR BOX					Locator

V1.1