

SHRINK TUBE PROTECT BOX25.4/12.7 TR

Article No.: 61742443

Shrink hose; Cable diameter: 1in - 0.5in; Polyolefin; transparent;



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Trade product, not a LAPP product.

Remarks

Trade product, not a LAPP product.

Technical Data

General information

Product type	Shrink hose
Type of packaging	Cardboard packaging

Delivery Unit	1
Industry segment	Solar

Electrical parameters

Product design

Total length	118.11 in
Panel type	Thin-walled
Wall thickness, shrunk	0.035 in
Material	Polyolefin
Perforated	No
Shrinkage range (min.)	1 in
shrinkage range (max.)	0.5 in
shrinking ratio	2:1
Colour description	transparent

Product features

shrinking temperature	90 °C
Flame-retardant	No
UV-resistant	No
Chemical resistant	Yes
Halogenfree	No
Oil resistant	No

Certifications and standards

EAC certified	Not required
EAC certification number	Отказное письмо № 18/1
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No

CSA certified	No
VDE certified	No

Shrink tube PROTECT

Article No.	Name	Shrinkage range (min.)	shrinkage range (max.)	Colour description	Total length	Delivery Unit
61742400	SHRINK TUBE PROTECT 1.2/0.6 BK	0.047 in	0.024 in	black	1,968.504 in	1
61742401	SHRINK TUBE PROTECT 1.6/0.8 BK	0.063 in	0.031 in	black	1,968.504 in	1
61742402	SHRINK TUBE PROTECT 2.4/1.2 BK	0.094 in	0.047 in	black	1,968.504 in	1
61742403	SHRINK TUBE PROTECT 3.2/1.6 BK	0.126 in	0.063 in	black	1,968.504 in	1
61742404	SHRINK TUBE PROTECT 4.8/2.4 BK	0.189 in	0.094 in	black	1,968.504 in	1
61742405	SHRINK TUBE PROTECT 6.4/3.2 BK	0.252 in	0.126 in	black	984.252 in	1
61742406	SHRINK TUBE PROTECT 9.5/4.7 BK	0.374 in	0.185 in	black	984.252 in	1
61742407	SHRINK TUBE PROTECT 12.7/6.4 BK	0.5 in	0.252 in	black	984.252 in	1
61742408	SHRINK TUBE PROTECT 19.1/9.5 BK	0.752 in	0.374 in	black	984.252 in	1
61742409	SHRINK TUBE PROTECT 25.4/12.7 BK	1 in	0.5 in	black	590.551 in	1
61742416	SHRINK TUBE PROTECT 3.2/1.6 GN/YE	0.126 in	0.063 in	green/yellow	1,968.504 in	1
61742417	SHRINK TUBE PROTECT 4.8/2.4 GN/YE	0.189 in	0.094 in	green/yellow	1,968.504 in	1
61742418	SHRINK TUBE PROTECT 6.4/3.2 GN/YE	0.252 in	0.126 in	green/yellow	984.252 in	1
61742419	SHRINK TUBE PROTECT 9.5/4.7 GN/YE	0.374 in	0.185 in	green/yellow	984.252 in	1
61742420	SHRINK TUBE PROTECT 12.7/6.4GN/YE	0.5 in	0.252 in	green/yellow	984.252 in	1
61742421	SHRINK TUBE PROTECT 19.1/9.5 GN/YE	0.752 in	0.374 in	green/yellow	984.252 in	1
61742422	SHRINK TUBE PROTECT 25.4/12.7 GN/YE	1 in	0.5 in	green/yellow	590.551 in	1
61742423	SHRINK TUBE PROTECT BOX 1.2/0.6 BK	0.047 in	0.024 in	black	472.441 in	1
61742424	SHRINK TUBE PROTECT BOX 1.6/0.8 BK	0.063 in	0.031 in	black	472.441 in	1
61742425	SHRINK TUBE PROTECT BOX 2.4/1.2 BK	0.094 in	0.047 in	black	472.441 in	1
61742426	SHRINK TUBE PROTECT BOX 3.2/1.6 BK	0.126 in	0.063 in	black	472.441 in	1
61742427	SHRINK TUBE PROTECT BOX 4.8/2.4 BK	0.189 in	0.094 in	black	393.701 in	1
61742428	SHRINK TUBE PROTECT BOX 6.4/3.2 BK 8M	0.252 in	0.126 in	black	314.961 in	1
61742429	SHRINK TUBE PROTECT BOX 9.5/4.7 BK	0.374 in	0.185 in	black	275.591 in	1
61742430	SHRINK TUBE PROTECT BOX 12.7/6.4 BK	0.5 in	0.252 in	black	236.22 in	1
61742431	SHRINK TUBE PROTECT BOX 19.1/9.5 BK	0.752 in	0.374 in	black	196.85 in	1
61742433	SHRINK TUBE PROTECT BOX25.4/12.7 BK	1 in	0.374 in	black	118.11 in	1
61742434	SHRINK TUBE PROTECT BOX 1.2/0.6 TR	0.047 in	0.024 in	transparent	472.441 in	1
61742435	SHRINK TUBE PROTECT BOX 1.6/0.8 TR	0.063 in	0.031 in	transparent	472.441 in	1
61742436	SHRINK TUBE PROTECT BOX 2.4/1.2 TR	0.094 in	0.047 in	transparent	472.441 in	1

Article No.	Name	Shrinkage range (min.)	shrinkage range (max.)	Colour description	Total length	Delivery Unit
61742437	SHRINK TUBE PROTECT BOX 3.2/1.6 TR	0.126 in	0.063 in	transparent	472.441 in	1
61742438	SHRINK TUBE PROTECT BOX 4.8/2.4 TR	0.189 in	0.094 in	transparent	393.701 in	1
61742439	SHRINK TUBE PROTECT BOX 6.4/3.2 TR	0.252 in	0.126 in	transparent	314.961 in	1
61742440	SHRINK TUBE PROTECT BOX 9.5/4.7 TR	0.374 in	0.185 in	transparent	275.591 in	1
61742441	SHRINK TUBE PROTECT BOX 12.7/6.4 TR	0.5 in	0.252 in	transparent	236.22 in	1
61742442	SHRINK TUBE PROTECT BOX 19.1/9.5 TR	0.752 in	0.374 in	transparent	196.85 in	1
61742443	SHRINK TUBE PROTECT BOX25.4/12.7 TR	1 in	0.5 in	transparent	118.11 in	1
61742449	SHRINK TUBE PROTECT-C 3.0/1.0 BK	0.118 in	0.039 in	black	472.441 in	1
61742450	SHRINK TUBE PROTECT-C 6.0/2.0 BK	0.236 in	0.079 in	black	354.331 in	1
61742451	SHRINK TUBE PROTECT-C 9.0/3.0 BK	0.354 in	0.118 in	black	236.22 in	1
61742452	SHRINK TUBE PROTECT-C 12.0/4.0 BK	0.472 in	0.157 in	black	212.598 in	1
61742453	SHRINK TUBE PROTECT-C 18.0/6.0 BK	0.709 in	0.236 in	black	141.732 in	1
61742454	SHRINK TUBE PROTECT-C 24.0/8.0 BK	0.945 in	0.315 in	black	118.11 in	1
61742460	SHRINK TUBE PROTECT-M 12/3 BK	0.472 in	0.118 in	black	590.551 in	1
61742461	SHRINK TUBE PROTECT-M 33/8 BK	1.299 in	0.315 in	black	393.701 in	1
61742462	SHRINK TUBE PROTECT-M 40/12 BK	1.575 in	0.472 in	black	196.85 in	1
61742463	SHRINK TUBE PROTECT-M 56/17 BK	2.205 in	0.669 in	black	118.11 in	1
61742464	SHRINK TUBE PROTECT-M 92/26 BK	3.622 in	1.024 in	black	39.37 in	1
61742465	SHRINK TUBE PROTECT SET					1

V1.1