

SILVYN® ELR SMOOTH 16.0X21.1 OG 30M

Article No.: 61751602

Protective cable conduit with plastic spiral; Inner diameter: 0.63in; Outer diameter: 0.831in; Nominal size: 20; Polyvinylchloride;



Details

Notes

Unless specified otherwise, the product values shown are rated values at room temperature. You can receive additional values, such as tolerances, upon request if they are available and have been released for publication.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

If applicable, the prices are solid metal prices without additional charges and VAT. Sales only to business customers.

Remarks

Technical Data

General information

Brand	SILVYN®
Product type	Protective cable conduit with plastic spiral
Delivery Unit	30

Electrical parameters
Product design

With bending protection	No
Bending protection fixed installation	No
Flexibly installed bending protection	No
Slotted	No
Resistance against hot swarf	No
Inner diameter	0.63 in
Outer diameter	0.831 in
Total length	1.181 in
Clear width	0.63 in
Nominal size	20 "
Lockable (two-part)	No
EMC shielding	No
Material conduit	Polyvinylchloride
Conduit material, short form	PVC
Coil material	Hard PVC
Conduit surface externally smooth	Yes
Smooth inner conduit surface	Yes
Colour description	orange
RAL color	RAL 2008

Product features

For permanent bending	No
IP protection rating	IP 68 - 2 g/cm ² IP 67
Suitable for EX-applications	No
Bending radius, static	2.756 in
Flame-retardant	No
UV-resistant	No
Acid-resistant	No

Halogenfree	No
Oil resistant	No
Impact proof	No

Certifications and standards

CE marking	Yes
UL recognized	No
UL listed	No
cUR recognized	No
cUL listed	No
CSA certified	No
VDE certified	No
Product standard according to IEC	IEC 61386-1 IEC 61386-23
GGVS certified	No
DNV-certified	No
Tested for fire protection for railway vehicles	No
Ecolab certified	No
NSF certified	No
FDA certified	No
EHEDG certified	No

SILVYN® ELR

Article No.	Name	Inner diameter	Outer diameter	Nominal size	Total length	Colour description	Delivery Unit
61751601	SILVYN® ELR SMOOTH 12.0X17.8 OG 30M	0.472 in	0.701 in	16 "	1.181 in	orange	30
61751602	SILVYN® ELR SMOOTH 16.0X21.1 OG 30M	0.63 in	0.831 in	20 "	1.181 in	orange	30

V1.1